

OUTDOOR ENCLOSURES

NEMA 4:

- **BW-1248BP**, 24"W x 24"H x 8"D with a 22"x22" removable interior back-panel, lock, two 1/4-turn latches, door-pocket, rain-channel, and exterior mounting ears
- **BW-1248BPW** the BW-1248BP with an air-tight/water-tight window in the door
- **BW-124BP**, 24"W x 24"H x 12"D with a 22"x22" removable interior back-panel, lock, two 1/4-turn latches, door-pocket, rain-channel, and exterior mounting ears
- **BW-124BPW** the BW-124BP with an air-tight/water-tight window in the door
- **BW-136BP**, 24"W x 36"H x 12"D with a 22"x34" removable interior back-panel, lock, two 1/4-turn latches, door-pocket, rain-channel, and exterior mounting ears
- **BW-136BPW** the BW-136BP with an air-tight/water-tight window in the door

Mier also has heated, fan-cooled, air-conditioned, or air-conditioned and heated versions of all these units. See our Temperature Controlled Enclosure line.

NEMA 3R:

- **BW-117**, 10"W x 12"H x 6"D with removable pad-lockable door and rain-shield
- **BW-118**, 6"W x 8"H x 4"D with a removable pad-lockable door and rain-shield
- **BW-119L**, 10"W x 12"H x 6"D with lock, two 1/4-turn latches, rain-shield, gasket and exterior mounting ears
- **BW-119LBP**, a BW-119L with a removable interior back-panel
- **BW-120**, 6"W x 8"H x 4"D with a 1/4-turn latch, rain-shield, gasket and exterior mounting ears

NEMA 1 Outdoor:

- **BW-120 DEPOSIT Box**, 14"W x 18"H x 10"D with a rain-shield, driop-down door which is hinged along the bottom, and a lock
- **BW-112 Siren/Speaker Box**, 8.55"W x 6.6"H x 5.55"D (siren/speaker not included)
- **BW-113 Siren/Speaker Box**, 7.25"W x 7.25"H x 6.25"D (siren/speaker not included)
- **BW-114 Siren/Speaker Box**, 11"W x 9.25"H x 6"D (siren/speaker not included)
- **BW-115/116 Siren/Speaker Box**, 11.3"W x 8.3"H x 10.5"D (siren/speaker not included)
- **BW-307 Bell Box with hinged door**, 13.5"W x 13.5"H x 4"D (bell not included)
- **BW-308 Bell Box with bolt-on door**, 13.5"W x 13.5"H x 4"D (bell not included)

BW-124BP



BW-117



BW-119L



BW-115/116



Also see our **Outdoor Polycarbonate Enclosures** which are **UL Listed, NEMA Rated** and are perfect for **outdoor, WiFi or corrosive environment installations.**

Don't see the enclosure you need?
Call or e-mail us and we'll be happy to help!

Other colors, graphic screening,
and customization are available
for quantities of 25 or more.



Indoor & Outdoor Electrical Enclosures | Drive-Alert Vehicle Detection & Asset Protection Systems | Custom Fabrication

800-473-0213 ~ info@mierproducts.com ~ www.mierproducts.com