

NEST_NC1103US

Power

AC power adapter: Input: 100-240VAC 0.2A Output: 5VDC 2.0A

Camera Input: 5VDC, 1.0A

Black

Nest Cam only

(No additional fees)

- 24/7, continuous 1080p HD streaming
- Motion alerts
- Sound alerts
- Night Vision
- Talk & Listen
- Clear Zoom
- Quick, easy setup
- Nest App
- Software updates over Wi-Fi

Get even more with Nest Aware

(Subscription sold separately)

- For \$10/month (or \$100/yr) per camera
- 10 days of 24/7, continuous, 1080p HD recording.
- (100+ GB of cloud storage)
- For \$30/month (or \$300/yr) per camera
- 30 days of 24/7, continuous, 1080p HD recording.
- (300+ GB of cloud storage)

PLUS:

• Alert summary to quickly scan your Video History.

- Activity Zones for personalized alerts.
- Powerful algorithms in the cloud to help filter out false alerts.
- Clips you can make, download, and share.
- Timelapses that turn hours of video into short films.

Languages	English French Dutch Spanish
Camera	1/3", 3 megapixel sensor with millions of colors and 8X digital zoom
Video	H.264 encoding, up to 1080p (1920 x 1080) at 30 frames/sec
Field of View	130° diagonal
Night Vision	8 High-power infrared LEDs (850nm) with IR cut filter
Audio and lights	Speaker Microphone RGB LED

Color

Features

Size and weight	Assembled Mass: 7.16 ounces (203 g) Height: 4.5 inches (11.4 cm) Width: 2.8 inches (7.3 cm) Depth: 2.8 inches (7.3 cm)
Connectivity requirements	Wi-Fi and working broadband Internet connection with at least 2 Mbps upload speed (DSL may not qualify)
	Phone or tablet with iOS 8 or later, or Android 4 or later (some phones and tablets do not support 1080p; viewing HD quality requires Wi-Fi)
	Free Nest Account
Wireless	Working Wi-Fi connection: 802.11 a/b/g/n @ 2.4GHz, 5GHz (WEP, WPA, WPA2 encryption supported) Bluetooth Low Energy (BLE)
Bandwidth requirements	At 720p, each camera requires an average of 200 kb/s of upload bandwidth and support for peak rates of 500 kb/s of upload bandwidth.
	At 1080p, each camera requires an average of 450 kb/s of upload bandwidth and support for peak rates of 1200 kb/s of upload bandwidth.
	If you subscribe to Nest Aware, your camera streams all video to the cloud for secure offsite storage. At 720p, this requires 60GB of upload bandwidth per month. At 1080p, this requires 140GB of upload bandwidth per month.
Green	Recyclable packaging
Operating Temperature	32-104°F (0-40°C)
Warranty	2-year limited warranty. For support, visit nest.com/support Our support team is also available by phone 24/7.
In the box	 Nest Cam indoor camera Stand 10-foot USB cable and power adapter Wall-mounting plate Nest screws Quick Start Guide Welcome Guide Window decal