



SPECIFICATION SHEET

385-FRZH



FR/AR FLEECE ZIP FRONT HOODIE

- PPE 2, ASTM F1506 and NFPA 70E
- Arc rating: ATPV=20.9cal/cm²
- 12 oz. FR fleece knit
- Aramid high tenacity FR thread
- One-way #5 resin zipper on aramid tape
- Adjustable FR drawstring around hood
- FR rib knit cuffs & waistband
- Hood with interlock lining
- 2 slash patch pockets at waist

APPLICATIONS

- Daily wear use and under arc flash suits and coveralls
- Electrical contractors and utilities
- Petrochemical
- Mining
- Hospital and plant technical maintenance
- HVAC
- Wind energy
- Hybrid auto mechanics
- Environmental remediation
- Welding
- Telecommunications/cable
- Emergency services

CARE INSTRUCTIONS

Machine wash warm, tumble dry low. Wash with synthetic detergents. Wash separate from everyday clothing in small loads. FR clothing is dry cleanable. DO NOT Bleach. DO NOT use fabric softener. DO NOT use dryer sheets.

TECHNICAL DATA

MATERIAL	12 oz. FR fleece knit, 100% Cotton
CONSTRUCTION	100% FR Cotton
COLOR	■ Navy, ■ Orange
SIZES	M-3X
PACKAGING	1 per polybag; 20 per case
CASE DIMENSIONS	25.2" x 18.9" x 16.5" / 64cm x 48cm x 42cm
CASE WEIGHT	41.9 lbs / 19 kg
COO	China


BARCODES

ITEM	BAG	BOX	CASE
■ 385-FRZH-NV/M	616314158483	01616314158482	02616314158481
■ 385-FRZH-NV/L	616314158490	01616314158499	02616314158498
■ 385-FRZH-NV/XL	616314158506	01616314158505	02616314158504
■ 385-FRZH-NV/2X	616314158513	01616314158512	02616314158511
■ 385-FRZH-NV/3X	616314158520	01616314158529	02616314158528
■ 385-FRZH-OR/M	616314158537	01616314158536	02616314158535
■ 385-FRZH-OR/L	616314158544	01616314158543	02616314158542
■ 385-FRZH-OR/XL	616314158551	01616314158550	02616314158559
■ 385-FRZH-OR/2X	616314158568	01616314158567	02616314158566
■ 385-FRZH-OR/3X	616314158575	01616314158574	02616314158573



DIMENSIONS (in/cm)

	M	L	XL	2X	3X
A	48 / 122	52 / 132	56 / 142	60 / 152	64 / 163
B	27.5 / 70	28.5 / 72	29.5 / 75	30.5 / 77	31.5 / 80



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | www.pipglobal.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.