



SPECIFICATION SHEET

39-1310



G-TEK® COTTON / POLYESTER GLOVE WITH LATEX COATED CRINKLE GRIP - ECONOMY GRADE

- Latex "Crinkle" coating provides superior grip in wet and dry conditions
- Knit Wrist helps prevent dirt and debris from entering the glove
- Seamless cotton/polyester knit shell is comfortable and flexible
- Ergonomic shaped curved finger pattern
- Breathable back for comfort
- This style is also available tri-folded and shrink-wrapped for carefree dispensing through vending machines (39-1310V)

APPLICATIONS

- Assembly
- Construction
- Inspection
- Material handling
- Refuse handling
- Landscaping
- Gardening

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry is not recommended.

TECHNICAL DATA

MATERIAL	Cotton/Polyester, latex			
COLOR	Shell: Gray / Coating: Blue			
CUFF STYLE	Continuous knit			
SIZES	S - XL			
PACKAGING	12 pair per dozen; 6 dozen per case			
CASE	S: 14.2" x 10.2" x 12.6" / 36cm x 26cm x 27.5cm			
	M: 15" x 11" x 12.6" / 36cm x 26cm x 28cm			
	L: 15" x 11" x 12.6" / 37cm x 27cm x 28.5cm			
	XL: 15.7" x 11.4" x 13" / 38cm x 28cm x 29cm			
CASE WEIGHT	S	M	L	XL
	14.1 lbs 6.4 kg	15.2 lbs 6.9 kg	16.1 lbs 7.3 kg	17 lbs 7.7 kg
COO	China			

PERFORMANCE PROPERTIES

EN388: 2243						
ABRASION	0	1	2	3	4	—
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	—
PUNCTURE	0	1	2	3	4	—


BARCODES

ITEM	BAG	DOZEN	CASE
39-1310/S	----	01616314010972	02616314010972
39-1310/M	----	01616314010989	02616314010989
39-1310/L	----	01616314010996	02616314010996
39-1310/XL	----	01616314011009	02616314011009



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.3 / 23.7	9.7 / 24.7	10.3 / 26.1	10.5 / 26.7
B	3.8 / 9.7	4.1 / 10.5	4.3 / 10.9	4.4 / 11.3



PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®

968 Albany Shaker Road | Latham, NY 12110 | 800-262-5755 | 518-861-0133 | Fax: 518-861-0144 | sales@pipusa.com | www.pipusa.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.