


EZ-RJ45® Connectors

The patented EZ-RJ45® connector simplifies twisted pair terminations by allowing the wires to be inserted through the connector and out the front, to easily verify the proper wiring order. Pulling the connector down over the cable jacket and seating it tightly in the rear of the connector, optimizes the performance of the termination. Terminate with the patented EZ-RJ45® Crimp Tools – crimp and trim in one cycle.



The EZ-RJPRO™ Termination Pod

P/N 90173

The complete field kit for the professional installer. Includes everything for consistent, repeatable and easier EZ-RJ45® installations.



Includes:

- EZ-RJPRO HD Crimp Tool
- Cat5e/6 Cable Jacket Stripper
- Electrician's Scissors
- EZ-RJ45 Cat5e – 100 pcs
- EZ-RJ45 Cat6 – 100 pcs
- EZ-RJ12/11 – 50 pcs

EZ-VIKING™ Crimp Tool

P/N 100544

For Data Centers, Aerospace & Broadcast

- Terminates EZ-RJ45® Cat5e/6, standard & shielded
- Parallel action for precision crimping
- High leverage ratchet action ensures full crimp cycle
- Highest quality/durability – minimum of 50,000 cycles



EZ-RJPRO™ HD

P/N 100054C

For the professional installer

- Crimps & trims in one cycle
- For EZ-RJ45® & EZ-RJ12/11 & standard modular plugs (except AMP)
- Clean trim on EZ-RJ45® conductors
- Ratcheted, high leverage platform for consistent terminations
- Tool steel die head provides 360° degree connector support during crimp
- Built-in wire cutter and stripper

EZ-RJ45® Crimp Tool

P/N 100004C

Terminate EZ-RJ45® connectors

- Crimp and trims in a single cycle
- For use with EZ-RJ45® Cat5/5e & Cat6 connectors
- Ratcheted straight action for consistent terminations
- Will also work on most other RJ11, RJ12 and RJ45 connectors (except AMP)

Snag Proof EZ Strain Reliefs

Designed specifically for the EZ-RJ45® plugs

- Prolongs patch cord life
- Maintain bend radiuses for standards compliance
- Terminations have a professional finished look
- No more snags or hang-ups, causing tangled messes
- Easier to unlock when unplugging from jack/port
- UL and RoHS compliant

Packaging Description/Quantity	EZ-RJ45®		EZ-RJ45® Cat5e/6		EZ-RJ12/11		EZ-RJ45® Strain Reliefs	
	Cat5/5e	Cat6	Internal	External	Standard/Tab	Long/Tab	Cat5/5e	Cat6
10 Piece Clamshell		100009C	100021C	100023C				
15 Piece Clamshell	100015							
50 Piece Clamshell	100003C	100010C	100020C	100022C	100026C	100026LTC	100035C	100036C
100 Piece Box	100003B	1000010B			100026B	100026LTB		
50 Piece Jar			202020J	202022J				
100 Piece Jar	202003J	202010J			202026J		202035J	202036J
50/50 Combo Jar (Includes EZ strain reliefs)	202015J	202016J						
50 Piece Bag			100020	100022			100035	100036
100 Piece Bag	100003BG		105020	105022				
500 Piece Bag	105003	105004			105005	105005LT	105015	105016