



TALKAPHONE

EMERGENCY PHONE MOUNTS

# ETP-WMS WALL MOUNT S CALL STATION SERIES



TALKAPHONE'S WALL MOUNT S EMERGENCY CALL STATION IS AN IDEAL SECURITY SOLUTION FOR REMOTE AND HIGH-RISK AREAS. THE STATION OFFERS CONTEMPORARY ARCHITECTURAL STYLING AND IS CONSTRUCTED OF DURABLE 316 MARINE GRADE STAINLESS STEEL. AN ALWAYS-LIT LED BLUE LIGHT PROVIDES HIGH VISIBILITY AND GIVES PASSERS-BY A SENSE OF SECURITY. USERS CAN CALL EMERGENCY PERSONNEL WITH A SIMPLE PUSH OF A BUTTON.

## FEATURES

- Attention-getting LED Blue Light is included and mounted inside a polycarbonate housing. The LED Blue Light is continuously lit and flashes for the duration of a call to draw attention to a unit when "EMERGENCY" button is pressed.
- Emergency Phone faceplate is illuminated at all times by an LED Panel Light (ETP-WMS only)
- Vandal-resistant marine grade 316 stainless steel construction
- Designed to resist extreme weather conditions
- A variety of signage, graphics, and color choices are available
- Easily mount any flush mounting Talkaphone ETP-400 Series, ETP-500 Series, VOIP-500 Series, or VOIP-600 Series Emergency/Information Phone into the unit (sold separately)
- ADA-compliant
- Economy option available (ETP-WMSE)

\*Call station sold separately

	<b>ETP-WMS - Wall Mount S</b>	<b>ETP-WMSE - Wall Mount S Economy</b>
		
<b>Construction:</b>	<i>Brushed marine grade (316) stainless steel with impact- and UV-resistant polycarbonate lens.</i>	<i>Brushed marine grade (316) stainless steel with impact- and UV-resistant polycarbonate lens.</i>
<b>Dimensions (W x H x H):</b>	<i>10 x 32 x 4 in. (253 x 810 x 101 mm)</i>	<i>10 x 32 x 4 in. (253 x 810 x 101 mm)</i>
<b>Weight:</b>	<i>23 lbs. (10.4 kg)</i>	<i>23 lbs. (10.4 kg)</i>
<b>Colors:</b>	<i>Brushed stainless steel is standard. Available painted in custom colors.</i>	<i>Brushed stainless steel is standard. Available painted in custom colors.</i>
<b>Lettering</b>	<i>2 in. high reflective red "EMERGENCY" lettering with wide-angle visibility is standard. Available as "ASSISTANCE", "INFORMATION", or custom lettering, colors and graphics.</i>	<i>2 in. high reflective red "EMERGENCY" lettering with wide-angle visibility is standard. Available as "ASSISTANCE", "INFORMATION", or custom lettering, colors and graphics.</i>
<b>Lighting:</b>	<i>LED Blue Light: 78 flashes per minute, 70% of initial lumens after 50,000 hours of operation. LED Panel Light: Ultra bright LEDs, 50,000 hour lifetime.</i>	<i>LED Blue Light: 78 flashes per minute, 70% of initial lumens after 50,000 hours of operation.</i>
<b>Power:</b>	<i>LED Blue Light: 12/24 VDC or 120 VAC LED Panel Light: 1.2 watts, 12-24 VDC/VAC, 120VAC</i>	<i>LED Blue Light: 12/24 VDC or 120 VAC</i>
<b>Mounting:</b>	<i>Mounts to a wall or straps to a pole or a kiosk.</i>	<i>Mounts to a wall or straps to a pole or a kiosk.</i>
<b>Shown With:</b>	<i>VOIP-600E</i>	<i>VOIP-500E</i>




**TALKAPHONE**

THE LEADERS IN SECURITY AND LIFE SAFETY COMMUNICATIONS

7530 North Natchez Avenue  
 Niles, Illinois 60714  
 Tel: 773-539-1100  
 Email: info@talkaphone.com  
 Web: www.talkaphone.com

**DIMENSIONAL DIAGRAMS: ETP-WMS**



All dimensions are in inches and are provided for reference only.



**TALKAPHONE**

THE LEADERS IN SECURITY AND LIFE SAFETY COMMUNICATIONS

**OPTIONS & ACCESSORIES**

Add to Model:	Description:
-OP2	Includes a housing for mounting your own fixed CCTV camera (Stand form factor with maximum camera depth of 3.5 in.) inside the wall mount above the emergency phone faceplate. Inquire for further details
-OP3	Includes an AXIS M1025 Network Camera inside the wall mount above the emergency phone faceplate.

**ACCESSORIES:**

**Pole Mounting Kit:**

Order ETP-PMKT Pole Mounting Kit for strapping ETP-WMS Series to a pole.

**Strapping Tool:**

Order ETP-PMKT-TOOL Strapping Tool for use with ETP-PMKT Pole Mounting Kit.