

ClickShare CSE-800

Wireless presentation and collaboration system for boardrooms and conference rooms



The CSE-800 was designed to bring the ClickShare experience to boardrooms, high-end meeting rooms, and conference rooms. Introducing a number of unique features, including simultaneous sharing of up to 8 people, automatic & manual moderation, and blackboarding & annotation, the CSE-800 is the most powerful system in the ClickShare family today. The CSE-800 was designed for enterprise rollouts and offers enhanced security features, a wider range of connectivity options – including AirPlay and Google Cast support for non-HDCP content – and central management.

The power of 2

The CSE-800 features two HDMI inputs and outputs. This means that there is a direct connection with legacy equipment and easy integration with conferencing systems, but also that two 4K DCI displays can be driven by a single base unit. Furthermore, the 2 network connections allow separate and simultaneous connection to multiple networks (e.g. guest and corporate networks), and provide additional security and convenience for users. Allowing up to 8 persons to share content simultaneously, the CSE-800 ensures connectivity to the central screen and encourages collaboration.

The moderation functionality was specifically designed for use in larger rooms, with multiple people wanting to share at the same time. To prevent the rapid switching of screens, making the content difficult to follow, a moderator can manually select which content appears on-screen and when, thus ensuring a great experience for all attendees. The moderation function can be switched off at any time, returning the system into ClickShare's normal operating mode, with content being shared upon the click of a button. For user convenience, security features of the CSE-800 can be set to one of three predefined levels, depending on the company's policies and needs.

Available in EMEA, US, Canada and China in Q2 of 2017. Other countries will follow quickly depending on certification.

Product specifications

ClickShare CSE-800

General specifications	
AirPlay Support	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 10.3 / Mac OS 10.11 El Capitan or higher
Operating system	Windows 7/8/8.1/10 32 & 64 bit Mac OSX 10.10/10.11/10.12 (Sierra) Android v5 & v6 (ClickShare app) iOS 8, 9 & 10 (ClickShare app)
Video outputs	2x HDMI
Video inputs	2x HDMI
Output resolution	4K DCI (4096x2160)
Input resolutions	4K DCI (4096x2160)
Frame rate	Up to 30 fps
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Number of sources simultaneous on screen	8 (4 per screen)
Number of simultaneous connections	64
Audio	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available (depending on the driver of your graphics card)
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/b/g/n and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	2x Ethernet LAN 2x USB 2.0; 2x USB 3.0 (back); 2x USB 3.0 (front) Audio analog line out & in on mini jack socket (3.5mm), digital S/PDIF
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard Possible to extend to 5 years
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	46.2mm x 282.3mm x 206.5mm (excl. antennas) / 1.8" x 11.1" x 8.1" 146.4mm x 282.3mm x 206.5mm (incl. antennas) / 5.8" x 11.1" x 8.1"
Power supply	Standard 110/220 V AC plug
Power consumption	Normal operation: 90W under full usage 52W under normal usage (connect 2 HDMI outputs, connect 1 HDMI input, share with 4 people) ECO mode: 30W Networked standby mode: < 1W Deep standby mode: < 0.5W
Weight	2.2kg / 4.85lbs

Last updated: 14 Jun 2017
Technical specifications are subject to change without prior notice.
Please check www.barco.com for the latest information.