

117-05350

HellermannTyton

Article Number: 117-05350

Description: Double-Head Cable Tie, 12" Long, 50lb Tensile Strength, PA66HS, Black, 1000/pkg



Base Data		
	Local Order Number	T50IDH0HSM4
	Type	T50IDH
	Color	Black (BK)
	Features and benefits	<ul style="list-style-type: none"> • Heat stabilized cable ties provide excellent resistance to high heat exposures. • The tie contains a dual locking design to secure two bundles at once. • Head design can also provide spacing between parallel bundles. • Bent tail allows for quick insertion into head.
	Quantity Per	bag
	Product Description	The double head cable tie was designed with a dual locking head to secure two bundles simultaneously. The head also provides separation between bundles or bundles running parallel to each other. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.
	Short Description	Double-Head Cable Tie, 12" Long, 50lb Tensile Strength, PA66HS, Black, 1000/pkg
Product Dimensions		
	Minimum Tensile Strength (Imperial)	50.0lbs
	Minimum Tensile Strength (Metric)	225.0N
	Length L (Imperial)	12.0"
	Length L (Metric)	305.0mm
	Bundle Diameter 2nd Loop Max. (Imperial)	1.5"
	Fixation Method	None
	Identification Plate Position	none
	Releasable Closure	No
	Tie Closure	plastic pawl
	Variant	Inside Serrated
	Width W (Imperial)	0.19"
	Width W (Metric)	4.7mm
	Bundle Diameter Min. (Imperial)	0.06"

117-05350



Product Dimensions	Bundle Diameter Min. (Metric)	1.6mm
	Bundle Diameter Max. (Imperial)	1.5"
	Bundle Diameter Max. (Metric)	76.0mm
	Bundle Diameter 1st Loop Max. (Imperial)	3.0"
	Thickness T (Imperial)	0.055"
	Thickness T (Metric)	1.4mm
Material and Specifications		
	Material	Polyamide 6.6 heat stabilized (PA66HS)
	Material Shortcut	PA66HS
	Flammability	UL 94 V2
	Halogenfree	Yes
	Operating Temperature	-40°F to +257°F (-40°C to +125°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	Certification/Specification	UL ANSI/UL 1565
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	1000
	Package Quantity (Metric)	1000Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	1.9kg