




# SPECIFICATION SHEET

## 56-425



### MAXIDRY® ULTRA LIGHTWEIGHT NITRILE GLOVE, ¾ DIPPED WITH SEAMLESS KNIT NYLON / LYCRA® LINER AND NON-SLIP GRIP

- Seamless string knit shell is comfortable and flexible
- Foam nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Increased resistance to oils via ATG's LiquiTech® technology
- Synthetic coating combined with an industry leading super light seamless knit liner
- Locking cuff ensures the glove doesn't slip on the hand.
- The micro-cup non-slip grip finish allows for a controlled and superior grip in oily and wet applications
- All ingredients used in the manufacturing and construction of this product are compliant with the REACH legislation
- Silicone free

### APPLICATIONS

- Precision handling in oily and wet environments
- Engine, power train, gear box, transmission, shock absorber assembly
- Handling small castings, small components, and parts
- General handling and maintenance

### CARE INSTRUCTIONS

Use commercial laundry soap or detergent (do NOT use dry cleaning solutions) Wash in warm to medium hot water, do not exceed 104°F (40° C). Wash for 10 minutes and rinse in cold water. Repeat wash and rinse if soiling is especially heavy. Tumble dry - maximum temperature 140°F (60° C).

### TECHNICAL DATA

|             |                                                  |                 |               |                 |               |
|-------------|--------------------------------------------------|-----------------|---------------|-----------------|---------------|
| MATERIAL    | Nitrile, nylon, Lycra®                           |                 |               |                 |               |
| COLOR       | ■ Purple / ■ Black                               |                 |               |                 |               |
| CUFF STYLE  | Continuous knit                                  |                 |               |                 |               |
| SIZES       | S - XXL                                          |                 |               |                 |               |
| PACKAGING   | 12 pairs per dozen, 6 dozen per case             |                 |               |                 |               |
| CASE        | 20.0" x 11.8" x 10.8" / 50.8cm x 30.0cm x 27.4cm |                 |               |                 |               |
| CASE WEIGHT | S                                                | M               | L             | XL              | XXL           |
|             | 15.4lbs / 7.0kg                                  | 16.5lbs / 7.5kg | 17.6lbs / 8kg | 18.7lbs / 8.5kg | 19.8lbs / 9kg |
| COO         | Sri Lanka                                        |                 |               |                 |               |

### PERFORMANCE PROPERTIES

|             |   |   |   |   |   |   |
|-------------|---|---|---|---|---|---|
| EN388: 4121 |   |   |   |   |   |   |
| ABRASION    | 0 | 1 | 2 | 3 | 4 | - |
| CUT         | 0 | 1 | 2 | 3 | 4 | 5 |
| TEAR        | 0 | 1 | 2 | 3 | 4 | - |
| PUNCTURE    | 0 | 1 | 2 | 3 | 4 | - |


### BARCODES

| ITEM         | BAG  | DOZEN          | CASE           |
|--------------|------|----------------|----------------|
| ■ 56-425/S   | ---- | 01616314117083 | 02616314117082 |
| ■ 56-425/M   | ---- | 01616314117076 | 02616314117075 |
| ■ 56-425/L   | ---- | 01616314117069 | 02616314117068 |
| ■ 56-425/XL  | ---- | 01616314117090 | 02616314117099 |
| ■ 56-425/XXL | ---- | 01616314117106 | 02616314117105 |



### DIMENSIONS (in/cm)

|                  | S          | M          | L          | XL         | XXL        |
|------------------|------------|------------|------------|------------|------------|
| A                | 9.8 / 25.0 | 9.8 / 25.0 | 9.8 / 25.0 | 9.8 / 25.0 | 9.8 / 25.0 |
| B                | 3.2 / 8.2  | 3.3 / 8.4  | 3.7 / 9.4  | 3.8 / 9.7  | 3.9 / 10.0 |
| Thickness: 1.3mm |            |            |            |            |            |



**PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®**

968 Albany Shaker Road | Latham, NY 12110 | 800-262-5755 | 518-861-0133 | Fax: 518-861-0144 | sales@pipusa.com | www.pipusa.com

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.