

151-00783

HellermannTyton



Article Number: 151-00783

Description: Side Convoluted Tubing Clip, Max Bundle Diameter .6", PA66HIRHS, Black, 5000/pkg

Base Data		
	Local Order Number	151-00783
	Type	CTCFT6
	Color	Black (BK)
	Features and benefits	• Clip includes an internal rib that spans the inside of the bracket to fit securely into the profile of the tubing to prevent lateral movement and slipping of the tubing. • Extended fir tree allows for a wide range of panel thicknesses. • Fir tree design provides low insertion forces and high extraction forces.
	Quantity Per	carton
	Product Description	Convoluted Tube Clips provide a quick and easy method for firmly securing corrugated covered cables and wires to a surface. Applications such as this can be found in a wide variety of industries such as the wire harness, automotive, trucking, and heavy equipment manufacturing industries.
	Short Description	Side Convoluted Tubing Clip, Max Bundle Diameter .6", PA66HIRHS, Black, 5000/pkg
Product Dimensions		
	Length L (Imperial)	0.43"
	Length L (Metric)	11.0mm
	Fixation Method	Fir Tree
	Width W (Imperial)	0.43"
	Width W (Metric)	11.0mm
	Height H (Imperial)	0.73"
	Height H (Metric)	18.5mm
	Height H2 (Imperial)	0.37"
	Height H2 (Metric)	9.3mm
	Bundle Diameter Min. (Imperial)	0.43"
	Bundle Diameter Min. (Metric)	11.0mm
	Bundle Diameter Max. (Imperial)	0.59"
	Bundle Diameter Max. (Metric)	15.0mm
	Panel Thickness Max. (Imperial)	0.03"

151-00783



Product Dimensions	Panel Thickness Max. (Metric)	4.5mm
	Panel Thickness Min. (Imperial)	0.04"
	Panel Thickness Min. (Metric)	0.7mm
	Mounting Hole Diameter D (Imperial)	0.25 - 0.28"
	Mounting Hole Diameter D (Metric)	6.3 - 6.7 mm
	Mounting Hole Diameter D Min. (Imperial)	0.25"
	Mounting Hole Diameter D Max. (Imperial)	0.26"
	Nominal Diameter (Imperial)	1-9/16"
	Nominal Diameter (Metric)	15.0mm
Material and Specifications		
	Material	Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)
	Material Shortcut	PA66HIRHS
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	5000
	Package Quantity (Metric)	5000Pieces
	Customs Number(Schedule B)	3926909987
	Content Unit (BMEcat)	pieces
	Weight (Metric)	2kg