

597-00031

HellermannTyton

Article Number: 597-00031



Description: Caution Write-On Self-Laminating Tag, Telephone Cable, 3.5" x 2.0", Yellow, 25/pkg

Base Data		
	Local Order Number	CT2012X2
	Type	CT2012
	Color	White (WH)
	Features and benefits	<ul style="list-style-type: none"> • Clear laminating plastic flap permanently protects the writing and data marked on the tag. • Mounting holes for easy mounting using standard cable ties. • Markers can be mounted in any direction, either vertically, horizontally, as a wrap-around identification plate or as a flag for the best visual position on the cable assembly.
	Quantity Per	pack
	Product Description	<p>HellermannTyton's Rite-On Markers are made from a flexible vinyl film and used to mark wire and cable. The self-laminating labels have a clear tail which seals the legend under clear vinyl, maintaining the quality of the labels. The Rite-On markers are packaged in a reusable dispenser made from high impact plastic which is resistant to oils and grease.</p> <p>Product Features</p> <ul style="list-style-type: none"> - Easily and conveniently fits in a pants or shirt pocket. - Once loaded, unit allows minimal label exposure to dust and moisture. - Can be used with standard ball point pens or HellermannTyton nylon marking pens. - Excess liner is easily cut-off by tearing it over the edge guide at the front of the unit. - The dispenser can be reloaded over and over again, making it a cost-effective and efficient method of labeling.
	Technical Description	Caution Write-On Self-Laminating Tag, Telephone Cable, 3.5" X 2.0", Yellow
Product Dimensions	Short Description	Caution Write-On Self-Laminating Tag, Telephone Cable, 3.5" x 2.0", Yellow, 25/pkg
	Length L (Imperial)	2.2"
	Length L (Metric)	55.8mm
	Width W (Imperial)	3.5"
	Width W (Metric)	88.9mm
	Height H (Imperial)	.25"
	Height H (Metric)	6.35mm
	Horizontal Repeat HR (metric)	6.35mm

597-00031



Product Dimensions	Horizontal Repeat HR (imperial)	.25"
	Vertical Repeat VR (imperial)	2.0"
	Vertical Repeat VR (metric)	50.8mm
Material and Specifications		
	Material	Polyvinylchloride (PVC)
	Material Shortcut	PVC
	Adhesive	Acrylic
	Adhesive Operating Temperature	-40°F to +302°F (-40°C to +150°C)
	Operating Temperature	-40°F to +266°F (-40°C to +130°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	25
	Package Quantity (Metric)	25
	Customs Number(Schedule B)	3919905060
	Labels per Column	1
	Labels per Row	1
	Labels per Sheet	1
	Content Unit (BMEcat)	pack
	Weight (Metric)	0.2kg