

uplink® 4500EZ



GSM Universal Cellular Alarm Communicator

For Primary Or Redundant Alarm Communications

The Uplink 4500EZ includes the latest GSM technology for the best performance and longest life cycle. Compatible with 3G and 4G cellular networks, the 4500EZ also operates on redundant networks for maximum reliability. The 4500EZ is designed as a summary event communicator. All major formats are supported for compatibility with virtually all alarm systems and central stations. Installation of the Uplink 4500EZ is remarkably easy with the use of a secure website and unit switch settings. Activation is instant and is available using the dealer website or by a live operator.

Uplink Advantages

Secure dealer website for activation, configuration, and management

Flat-rate billing with no overage charges

Programmable periodic test intervals

Works with virtually any central station

Uplink Remote for interactive control and end-user notifications

Mobile activation and signal strength with Uplink Installer™

Live technical and activation support*

Uplink 4500EZ Device Feature:

- ✓ Primary or redundant alarm communications for residential or commercial security
- ✓ Supports virtually all security systems and multiple formats
- ✓ Programmable monthly, weekly, or daily status and signal tests
- ✓ Power from the panel or separate 12V DC power supply (not included)
- ✓ Two web configurable outputs
- ✓ Web and smartphone apps for remote arming and disarming
- ✓ Installs in minutes with reliable end-to-end signal verification

Canadian Model # 4500EZ CN


*8:00 a.m. to 8:00 p.m. EST, Monday through Friday
Specifications subject to change without notice.

(888) 9-UPLINK | (888) 987-5465 | www.uplink.com | sales@uplink.com

A **Numerex** Solution



4500EZ GSM Universal Cellular Alarm Communicator



A Trusted Partner

Uplink, a Numerex Solution, is the security industry's most trusted source for wireless alarm communicators. Uplink delivers the unique combination of technology, quality, options, and superior value that have made us the industry's trusted source for security solutions since 1996.

With hundreds of thousands of installed devices throughout the United States, Mexico, and Canada, Uplink has the experience and expertise to provide reliable, award winning products with first class support.

Uplink technology is certified by the ISO/IEC27001 information security management standard and backed by a web-based dealer support management tool.

For more information, visit the Uplink website at uplink.com.

Technical Specifications

INPUTS	
Four Inputs	<ul style="list-style-type: none">• Input 1: Connect to siren/bell (distinguishes between burg/steady and fire/pulsed) or programmable to 12 volts• Inputs 2-4: 12 volts
OUTPUTS AND REPORTING	
Central Station	<ul style="list-style-type: none">• Contact ID, SIA, Pulse 4/2 and Modem IIe/IIla²• Internet or Dial-up
Relay Outputs	Two — configurable
Testing	Monthly, weekly, or daily
Other Reporting	<ul style="list-style-type: none">• Low voltage• Email alerts to customer or alarm company
Status LEDs	<ul style="list-style-type: none">• Network• Service• Communications
RADIO	
4G (HSPA+)	Compatible with 2G, 3G and 4G GSM networks
Cellular Frequencies	850/1900 MHz
Transmit Power	Maximum allowable: <ul style="list-style-type: none">• 1.0W at 1900 MHz• 2.0W at 850 MHz
DIMENSIONS	
Height/Width/Depth (inches)	4.75/3.3/1.3
POWER SOURCE — NOT INCLUDED	
Power Requirements	12V DC 500 mA max on transmit 28mA standby
OPTIONAL ACCESSORIES	
Magnet mount antenna with 9ft cable - part number 1004ANT 8 inches tall high gain antenna with articulating joint — part number 1005ANT	

12V DC Required

Specifications subject to change without notice.

(888) 9-UPLINK | (888) 987-5465 | www.uplink.com | sales@uplink.com

A **Numerex** Solution

