

QUANTUM

IP WEB BROWSER TELEPHONE ENTRY SYSTEM
QC SERIES



Commercial application telephone entry system, programmable via Web Browser.

No "Software Installation" necessary

No "Monthly Fee"

Four way to program, via LAN, WAN, Direct Connect or System's Keypad.

Selectable port, no "Dedicated Static IP" needed.

Surface or Full-Flush Mount

FEATURES/MODEL	QC1 Surface	QC1FF Full Flush	QC1IP Surface	QC1IPFF Full Flush	QC2IP Surface	QC2IPFF Full Flush	QC6IP Surface	QC6IPFF Full Flush
QWCM IP Browser	optional	optional	●	●	●	●	●	●
Input power 12Vac transformer supplied	12Vac/12Vdc	12Vac/12Vdc	12Vac/12Vdc	12Vac/12Vdc	12Vac/12Vdc	12Vac/12Vdc	12Vac/12Vdc	12Vac/12Vdc
Current consumption	900mA	900mA	1150mA	1150mA	1150mA	1150mA	1150mA	1150mA
Operating temperature	0-140 °F	0-140 °F	0-140 °F	0-140 °F	0-140 °F	0-140 °F	0-140 °F	0-140 °F
1x16 Backlit LCD display	●	●	●	●	●	●	●	●
Backlit keypad button	●	●	●	●	●	●	●	●
Tenant capacity	100	100	100	100	250	250	600	600
Access code capacity 4-8 digit	300	300	300	300	1000	1000	600	600
Card/Fob capacity	300	300	300	300	1000	1000	3000	3000
Number of Built-inrelay form C dry contact	2	2	2	2	2	2	2	2
26-Bit wiegand input	●	●	●	●	●	●	●	●
Built-in 26-Bit <i>proprietary</i> card reader	●	●	●	●	●	●	●	●
10 - Time Zone								
10 - Auto unlock schedule								
20 - Holiday time zone								
10 - Unlock hold card								
10 - Unlock hold code 4-8 digit								
10 - Temporary card up to 10 times used								
10 - Temporary code 4-8 digit up to 10 times used								
2 - Auxiliary input for exit switch, postal lock								
2 - Door sensor								
Unlock hold timer	●	●	●	●	●	●	●	●
Event recording buffer	600	600	600	600	600	600	600	600
Satellite Keypad, Card Reader or Combo w/ independent access	max. 8	max. 8	max. 8	max. 8	max. 8	max. 8	max. 8	max. 8
Surface mount dimension	6-7/16"(H) x 10-3/8"(W) x 2-3/4"(D)							
Full-flush mount dimension	Outside: 9-13/16"(H) x 11-13/16"(W) Inside: 7-1/2"(H) x 10-1/2"(W) x 3"(D)							
Warranty	24 month	●Included						
ACCESSORIES								
QVPC Analog color camera USCR 26-Bit Wiegand Satellite Card Reader USKP Satellite keypad UFOB Quantum Keyfob UCLAM Quantum Clam Shell Card UIISO Quantum ISO Card UCRM 26-Bit Wiegand/RS-485 controller Module UWCR 26-Bit Wiegand Reader			Pedestal Mounting Post, Adapter Plate and Mounting Ring UPM1S Standard Single Arm (42"H, 5"x5" base) UPM4S Standard Single Arm (47"H, 5"x5" base) UPM1L Large Single Arm (47"H, 8"x8" base) UPM6L Large Single Arm (64"H, 8"x8" base) UPM2 Double Vertical Arm (44"/84"H, 8"x8" base) UPM5 Double Horizontal Arm (47"H, 8"x8" base) UPM12E 12" Expansion Arm use for all UPM UPMDB64 Single Arm Direct Buriel (64"H)			Miscellaneous Accessories USP1 AC and Telephone Surge Protector. USP2L Surge and Lighning Protection, include Lightning on 24 months warranty UBAT1 12VDC 4.5 Ahr backup battery. UXIT Multipurpose pust button switch Specifications and Warranty subject to change without prior notice		