

332RS6W



Products Low Voltage Products and Systems Industrial Plugs and Sockets Tough & Safe Surface Socket Outlets

General Information

Extended Product Type:	332RS6W
Product ID:	2CMA167180R1000
EAN:	7392696671804
Catalog Description:	Ind. P&S#332RS6W
Long Description:	Surface socket-outlet, earthing sleeve position 6h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

Additional Information

Additional Information:	3P+E
Cable Cross-Section:	2.5 ... 10 mm ²
Color:	Red
Connection Type:	Screw clamp
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP67 / IP69
E-nummer:	2416555
EAN:	7392696671804
ETIM 4:	EC001321 - CEE socket outlet
ETIM 5:	EC001321 - CEE socket outlet
ETIM 6:	EC001321 - CEE socket outlet
Enclosure Material:	Thermoplastic polyester (PBT)
Environmental Information:	2CMC700001D0002
Frequency (f):	60 Hz
Function:	Surface socket outlet
Gross Weight:	0.52 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#332RS6W
Minimum Order Quantity:	1 piece
Number of Poles:	4
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696671804
Package Level 1 Gross Weight:	0.6 kg
Package Level 1 Height:	200 mm
Package Level 1 Length:	140 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	135 mm
Product Main Type:	TRS
Product Name:	Wall mounted socket
Product Net Depth:	178 mm
Product Net Height:	178 mm

Product Net Length:	129 mm
Product Net Weight:	0.512 kg
Product Net Width:	99 mm
Protection Type:	Watertight
Rated Current (I_n):	32 A
Rated Voltage (U_r):	380 ... 415 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
SEMKO Certificate:	1613211
Selling Unit of Measure:	piece
Short Description:	Surface socket-outlet, 6h, 32A, IP67, 3P+E
Size:	125X99X188
Standards:	IEC 60309-1 IEC 60309-2
Suitable For:	Surface Socket Outlets
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour
RAL Number:	RAL 7001 - Silver Grey

