

Conference Calls with Style and Reach



Sennheiser Speakerphone Series
SP 220 UC



SENNHEISER SP 220 UC

The Sennheiser SP 220 UC is a UC optimized, portable, dual speakerphone solution that brings the conference closer, within reach of every participant. Designed for professionals requiring flexible and scalable conferencing solutions. It instantly connects via PC, mobile phone or tablet and is ideal for effortlessly creating high-quality audio conferences – from small huddle rooms to larger meeting rooms. Building on the award winning Sennheiser Speakerphone Series, the SP 220 UC dual speakerphone adds reach and style to any conference room, allowing more users to experience excellent Sennheiser sound quality and voice clarity.

Award winning design – sounds as good as it looks

Appearances matter – and the SP 220 UC shows its pedigree through looks alone. With their award winning iconic design, SP 220 UC's speakerphones are ideal for modern conference facilities where style is at a premium and audio clarity is a must. They are perfect for quality conscious professionals who need to set up larger conferences on the go. Requiring a minimum of table space, the Sennheiser SP 220 UC's streamlined styling and superb finish signal high-end quality.

Sound leadership – superb conference sound

Building on Sennheiser's 70 years of sound excellence, the SP 220 UC ensures the most natural listening experience in important business calls and conferences for both speakers and listeners. With Sennheiser Voice Clarity and the performance from two syn-

chronized speakerphones placed within reach of each participant, you can be confident you can be heard. Thanks to unique software, which allows the two speakerphone units to work together seamlessly, the SP 220 UC ensures that everyone can speak naturally and communicate back and forth with ease. And to ensure better interaction with colleagues and customers, distracting room sound reflections are removed so that voices sound like you are sharing the same room. In addition, the speakerphones offer stereo sound.

User focus

– quick to connect, simple to use

When you are in a hurry, it just has to work. Whether you use only one of the units for personal calls or two together for a full size conference, the SP 220 UC is the easiest and most flexible solution on the market. Just plug, play and communicate: Sennheiser SP 220 UC's built-in cable system connects directly to PC, mobile phone or tablet to provide high-quality audio communication. With the included coiled adapter, two synchronized speakerphones can be positioned up to 2.1 meters apart. Additional features include intuitive fingertip controls, long talk time and protective carrying pouches.

Benefits and key features:

- UC compatibility – optimized with major UC and softphone brands
- Compact and portable – premium, lightweight design for professionals needing a scalable conferencing solution they can set up anywhere
- Flexible – connect a speakerphone to your mobile phone, or cover a medium sized

conference room – with just one solution


- Outstanding communication – Sennheiser Voice Clarity for a natural speech and listening experience
- Better quality conferencing – places a speakerphone within reach of every participant for a superior quality audio experience for up to 12 participants
- Exceptional sound – with Sennheiser HD sound quality
- Be heard clearly – advanced signal processing removes room echo and controls reverberation
- Better interaction – dual talk function and close proximity microphones let you converse naturally without raising your voice
- Stereo sound for music – enjoy music wherever you are
- Plug and play in any situation – connect to both PC and mobile phone or tablet and you are ready to talk*
- Conferencing across devices – merges PC/softphone and mobile calls into one conference*
- Intuitive user interface – clear microphone mute button, call and volume control and easy cable management
- Long talk time – up to 20 hours with 2 ½ hours charging
- Voice prompts for low battery warning – always sufficient talk time
- Convenient, protective carry pouches
- Safe to leave on your desk – with optional security cable lock
- Peace of mind – 2 years of international warranty

* When the speakerphone is connected to a mobile phone or merges a call from a mobile phone, only one speakerphone unit is in use

Product Information

Product name	SP 220 UC			
Art. No.	507210			
EAN No.	40 44155 21503 8			
UPC No.	6 15104 28166 0			
Product description	High-end, daisy-chain UC speakerphone from individual use to midsize conference rooms			
General Data				
Talk time	Up to 20 hours			
Charging time	2 h 30 min			
Standby time	Up to 72 hours (active standby), up to 30 days (energy saving sleep)			
Weight	210 g / 7.35 oz (per speakerphone)			
Dimensions	110 x 30 mm / 4.33 x 1.18 in (per speakerphone)			
USB	Version 2.0			
Connectivity	PC via USB; Tablet and mobile phone via 3.5 mm jack cable* Dual operation between speakerphone via 3.5 mm jack cable and SP Link Adapter.			
Supported operating systems	Windows and Mac			
Microphone				
Microphone type	Omni Electret Condenser Microphone			
Frequency response	150–6.800 Hz			
Microphone coverage	360 degrees			
Speaker				
Speaker type	Dynamic, neodymium magnet			
Frequency response – multimedia	150–15.000 Hz			
Audio performance	Dynamic equalizer for communication and optimized stereo audio for music. Full duplex audio and echo cancellation for communication.			
Packaging				
Dimension of product packaging (L x W x H)	252 x 122 x 50 mm / 9.92 x 4.80 x 1.97 in			
Package weight (incl. complete product and packaging)	622 g / 21.94 oz			
Units in distributor master carton	10 pcs			
Master carton weight incl. products	7.48 kg / 16.49 lb			
Dimension of master carton (L x W x H)	600 x 345 x 155 mm / 23.62 x 13.58 x 6.10 in			
Unit pack/end user	1			
Content of delivery				
Box content	- Two speakerphones (SP 20 D UC) with integrated USB cable and 3.5 mm jack cable - SP Link Adapter - Two carry pouches - Safety guide - Quick guide			
Accessories & spare parts				
Product name	Product description	Art. No	EAN No.	UPC No.
Pouch – SP Series	Speakerphone protection pouch	506051	40 44155 09044 4	6 15104 25078 9
SP Link Adapter	Connect two speakerphones	506521	40 44155 20825 2	6 15104 27187 6
3.5 mm mini jack adaptor	Mobile adaptor cable	506052	40 44155 09045 1	6 15104 25079 6
3.5 mm to 2.5 mm Adapter	DECT handset adapter cable	506488	40 44155 20398 1	6 15104 26591 2
CEXT 02	USB to USB extension cable	502524	40 44155 03079 2	6 15104 14505 4
Security Cable Lock	Secure speakerphone to workspace (Kensington Slot)	506491	40 44155 20419 3	6 15104 26614 8
USB Power Supply	Multi-region USB power supply for EU/UK/US/AU	506475	40 44155 20351 6	6 15104 19142 6
Warranty	2 years			

* Please check Sennheiser Compatibility Guide at www.sennheiser.com/headsetcompatibility for mobile phone compatibility



Experience Sennheiser

Perfection is always relative: Users have different expectations from their headsets and speakerphones depending on their needs. For professional users, that need is to communicate as effectively as possible.

With Sennheiser's range of headsets and speakerphones, the combination of exceptional HD sound, quality design and build – and a focus on real life usability – give the best performance possible in busy offices, call centers and Unified Communications environments.

Please visit us at: www.sennheiser.com/cco



Sennheiser is one of the world's leading manufacturers of headphones, microphones, wireless transmission systems and high-quality headsets for both business and entertainment.

Drawing on the electro acoustics expertise of Sennheiser and the leading hearing healthcare specialist William Demant, Sennheiser Communications' wireless and wired headsets and speakerphones for contact centers, offices and Unified Communications professionals are the result of Sennheiser's and William Demant's joint leadership in sound quality, design, wearing comfort and hearing protection.

For further information, please visit:
www.sennheiser.com/cco

Sennheiser Communications A/S

Industriparken 27 · DK-2750 Ballerup · Denmark