



CT-2940/ST • CT-2940/STINT • CT-2940/STUK  
• CT-2940/STAUS • CT-2940/TO

CRIMP TOOL

This tool meets requirements of Safety for Hand Heldheld, Motor-Operated Electric Tools specification UL 60745-1 and CSA C22.2 No 60745-1. Tool is listed under CSA file number 268531.

**NOTES, UNLESS OTHERWISE SPECIFIED:**

The CT-2940/ST, CT-2940/STINT, CT-2940/STUK, CT-2940/STAUS and CT-2940/TO Battery Operated Crimping Tools are designed to crimp:

- Crimps Panduit Copper and Aluminum compression connectors using Panduit Crimping Dies. Go to [www.panduit.com](http://www.panduit.com) for more information.

**The CT-2940/ST, CT-2940/STINT, CT-2940/STUK and CT-2940/STAUS Tools include:**

Qty.	Description / Item
1	Battery Operated Hydraulic Crimp Tool
2	Rechargeable Battery (Makita Lithium-Ion 18VDC, 3Ah)
1	Makita Battery Charger – Regional (reference images below for regional plug type)
	<div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;"> <p>Plug Type A (North America)</p> </div> <div style="text-align: center;"> <p>Plug Type C (International)</p> </div> <div style="text-align: center;"> <p>Plug Type G (UK)</p> </div> <div style="text-align: center;"> <p>Plug Type I (Australia)</p> </div> </div>
1	Plastic Tool Case with Die Storage
1	Tool Carrying Strap
1	Set of Panduit “CD-940-DAPT” Die Adapters
1	Assist Handle (Not Shown)

**The CT-2940/TO Tool includes:**

Qty.	Description / Item
1	Battery Operated Hydraulic Crimp Tool
1	Set of Panduit “CD-940-DAPT” Die Adapters

**Technical Information:**

Tool Weight (including battery)	15.7 lbs. (7.1 kg)
Dimensions (including battery)	16.22” L x 12.56” H x 2.91” W [412 L x 319 H x 74 W] mm
Crimping Force	15 tons (135 kN)

Tools are to be used with Panduit crimp dies, and are sold separately. Go to [www.panduit.com](http://www.panduit.com) for more information.

A copy of the operation manual and accessory information can be found at: [www.panduit.com](http://www.panduit.com).

Dimensions in [brackets] are in millimeters. All dimensions are for reference only.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	<b>CT-2940/ST, CT-2940/STINT, CT-2940/STUK, CT-2940/STAUS and CT-2940/TO</b>				CUSTOMER DRAWING	
00	7-25-16	BKA	ACC	JADE	DRAWING RELEASED	010819	ITEM REVISION NAME: 00084SLD_DC/00				<b>PANDUIT</b>	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.x) ± --- (.xxx) ± --- (.xx) ± --- ANGLES ± ---				MATERIAL: -----	
							THIRD ANGLE PROJECTION				DRAWING NUMBER: 00084SLD_DC	
							DRAWN BY: BLR	DATE: 7-21-16	CHK BJPU	SCALE NONE	SHT 1 OF 1	SIZE B