

CP1-12R-10



Products Low Voltage Products and Systems Control Products Pilot Devices Pilot Devices - Compact Range

General Information

Extended Product Type:	CP1-12R-10
Product ID:	1SFA619100R1211
EAN:	7320500381519
Catalog Description:	PUSHBUTTON#CP1-12R-10#110-130V AC
Long Description:	Compact Pushbutton - Momentary - Flush - Red - Illuminated - Black plastic - 1NO

Additional Information

ABB Industrial IT Suite:	Control IT
Actuator Type:	Flush
Additional Information:	Ill. PB
Ambient Air Temperature:	Operation -25 ... +70 °C
Bezel Material:	Black plastic
Block:	1NO
Color:	Red
Country of Origin:	China (CN)
Customs Tariff Number:	85369001
Data Sheet, Technical Information:	1SFC151004C0201
Declaration of Conformity - CE:	1SFA1-70
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP20
E-nummer:	3717261
EAN:	7320500381519
ETIM 4:	EC002024 - Accessories for control circuit devices
ETIM 5:	EC001028 - Push button, complete
ETIM 6:	EC001028 - Push button, complete
Environmental Information:	1SFC151009D0201
Function:	Momentary
Illumination:	Illuminated
Instructions and Manuals:	1SFC151004C0201
Invoice Description:	PUSHBUTTON#CP1-12R-10#110-130V AC
Lamp Type:	LED 110-130V AC
Lens Color:	Red
Lower Button Color:	Red
Mechanical Durability:	0.5 million
Minimum Order Quantity:	10 piece
Number of Auxiliary Contacts NO:	1
Object Classification Code:	S
Order Multiple:	1 piece
Product Main Type:	CP1
Product Name:	Pushbutton
Product Net Depth:	0.055 m
Product Net Height:	0.030 m
Product Net Weight:	0.018 kg
Product Net Width:	0.030 m
Product Range:	Compact
Product Type:	CP

Rated Frequency (f):	50 / 60 Hz
Rated Operational Current AC-15 (I_a):	(120 V) 1.5 A (240 V) 1 A
Rated Operational Current DC-13 (I_a):	(24 V) 0.3 A (125 V) 0.2 A
Rated Operational Voltage:	110...130 V AC/DC
RoHS Date:	0626 5
RoHS Information:	1SFC151012D0202
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Selling Unit of Measure:	piece
Short Description:	Red Compact Pushbutton

