

Weatherproof Outlet Covers

ALUMINUM BLANK BOX WEATHERPROOF COVERS WITH GASKETS UL LISTED FOR WET LOCATIONS




TP7292 – TP7294




TP7296 – TP7298

Product Number	Description	Color	Std. Unit Carton	Wt. Lbs Per 100
TP7292	One Gang	Gray	100	8.3
TP7293	One Gang	White	100	8.3
TP7294	One Gang	Bronze	100	8.3
TP7296	Two Gang	Gray	50	12.5
TP7297	Two Gang	White	50	12.5
TP7298	Two Gang	Bronze	50	12.5


ROUND AND RECTANGULAR WEATHERPROOF COVERS WITH GASKETS, ZINC DIE-CAST, UL LISTED FOR WET LOCATIONS




TP7300 – 7302




TP7304 – 7306




TP7308 – 7310




TP7312 – 7314



TP7316 – 7318



TP7320 – 7322




TP7158 – 7160

Product Number	Description	No. of Outlet Holes	Color	Std. Unit Carton	Wt. Lbs Per 100
TP7300	4 1/2" Round	1-1/2"	Gray	25	20.8
TP7301	4 1/2" Round	1-1/2"	White	25	20.8
TP7302	4 1/2" Round	1-1/2"	Bronze	25	20.8
TP7304	4 1/2" Round	2-1/2"	Gray	25	33.3
TP7305	4 1/2" Round	2-1/2"	White	25	33.3
TP7306	4 1/2" Round	2-1/2"	Bronze	25	33.3
TP7308	4 1/2" Round	3-1/2"	Gray	25	33.3
TP7309	4 1/2" Round	3-1/2"	White	25	33.3
TP7310	4 1/2" Round	3-1/2"	Bronze	25	33.3
TP7312	Rectangular	1-1/2"	Gray	25	33.3
TP7313	Rectangular	1-1/2"	White	25	33.3
TP7314	Rectangular	1-1/2"	Bronze	25	33.3
TP7316	Rectangular	2-1/2"	Gray	25	33.3
TP7317	Rectangular	2-1/2"	White	25	33.3
TP7318	Rectangular	2-1/2"	Bronze	25	33.3
TP7320	Rectangular	3-1/2"	Gray	25	33.3
TP7321	Rectangular	3-1/2"	White	25	33.3
TP7322	Rectangular	3-1/2"	Bronze	25	33.3
TP7158	Blank Round	—	Gray	50	20.8
TP7159	Blank Round	—	White	50	20.8
TP7160	Blank Round	—	Bronze	50	20.8


Dimensional Data

Two Gang, Duplex Receptacle Covers




TP7228

Single Gang, GFCI Covers
Horizontal Mount




TP7236 - TP7238

Single Gang, GFCI Covers
Vertical Mount




TP7240 - TP7242

Two Gang, GFCI Covers




TP7248

Blank Covers




TP7292 - TP7294

Blank Covers




TP7296 - TP7298

Blank Covers




TP7158

Single Gang, Switch Covers
Vertical Mount




TP7256

Lampholders




TP7162 - TP7165

Hooded Lampholder




TP7178

Rectangular Lampholder Covers



TP7312 - TP7322

Round Lampholder Covers



TP7300 - TP7310