



Flexco® Bolt Solid Plate Fasteners

INSTALLATION TOOLS*

HAND & POWER TOOLS

	DESCRIPTION	FOR FASTENER NUMBER	ORDERING NUMBER	ITEM CODE	WT. KGS.
HAND TOOLS	BOLT HORN		2BH	30480	0.05
	BOLT BREAKER (Two Per Package)	1,140,190 & RP1 1½, 2, 2¼ & RP2 2½ & 3	110 112* 113*	30474 30475 30479	0.5 0.6 0.9
	PUNCH	1,140,190 & RP1 1½, 2, 2¼ & RP2 2½ & 3	P1P P2P P3P	30460 30461 30462	0.05 0.1 0.1
	BORING BIT	1,140,190 & RP1 1½, 2, 2¼ & RP2 2½ & 3	B1B B2B B3B	30468 30469 30470	0.05 0.05 0.05
	WRENCH	1,140,190 & RP1 1½, 2, 2¼ & RP2 2½ & 3	S1S** S2S S3S	30442 30443 30444	0.1 0.1 0.1
POWER TOOLS	POWER PUNCH	1,140,190 & RP1 1½, 2, 2¼ & RP2 2½ & 3	HP1 HP2 HP3	30463 30464 30465	0.1 0.1 0.1
	POWER BORING BIT	1,140,190 & RP1 1½, 2, 2¼ & RP2 2½ & 3	HB1 HB2 HB3	30471 30472 30473	0.05 0.05 0.05
	POWER WRENCH GREEN RED BLUE	1,140,190 & RP1 1½, 2, 2¼ & RP2 2½ & 3	HW1** HW2 HW3	30447 30448 30449	0.1 0.1 0.2
	QUICK CHANGE CHUCK		5552	30481	0.2
	12.5 mm (1/2") IMPACT TOOL (For Use with Quick Change Chuck)		30453	30453	8.9

* Sizes 112 & 113 are straight bolt breakers – no bend.

** For use with slotted nuts only.

*HD Installation Tools:

For HD Installation Tools, the discount is the standard BCP discount.

FLEXCO-LOK®

Belt tape 30.5 M (100') per carton

FASTENER SIZE	ORDERING NUMBER	ITEM CODE	WT. KGS.	TAPE WIDTH
Nos. 140, 1	FL7C	30888	0.4	11 mm (7/16")
Nos. 190	FL11C	30889	0.5	17 mm (11/16")
1-1/2, 2, 2-1/4				

CRACKING CHISEL

NUT SIZE	ORDERING NUMBER	ITEM CODE	WT. KGS.
1, 140 or 190	C1C	30438	0.5
1-1/2, 2, 2-1/4	C2C	30439	0.5

FLEXCO® BELT GROOVER

(11 mm (7/16") wide groove path.)

ORDERING NUMBER	ITEM CODE	WT. KGS.
FBG1	31978	0.8
EXTRA BLADES		
HSP3	31980	0.05

FLEXCO® SILICONE LUBRICANT

ORDERING NUMBER	ITEM CODE	PKG. QTY.	WT. KGS.
SLP5	30923	1	0.6

FLEXCO® BELT IDENTIFICATION TOOL

ORDERING NUMBER	ITEM CODE	WT. KGS.
BT-1	31075	0.03

