

Opt-X[®] SDX Wall-Mount Enclosures Small, Medium, and Large

APPLICATION

Opt-X SDX Wall-Mount Enclosures allow for inter-connect or cross-connect between cable and active equipment while using minimum wall space. The enclosure features and design allow for easy field termination of connectors, splicing, or pre-terminated plug-and-play solutions. The fiber enclosures are primarily used in controlled indoor applications, such as in entrance facilities, equipment rooms, and telecommunications rooms.



Small Wall-Mount



Medium Wall-Mount

Large Wall-Mount



SPECIFICATION

Opt-X SDX Wall-Mount Enclosures shall be available in multiple sizes to accommodate field connector termination, heat-fusion splicing, and plug-and-play MTP® cassettes for up to 288 fibers (LC). Large-size enclosures can be retrofitted in the field to a splice-only configuration for up to 576 heat-fusion single or 1728 Ribbon splicing. Enclosures can be oriented for left- or right-side patching to provide added flexibility. Adapter bulkhead shall accept Opt-X SDX Precision-Molded Adapter Plates, SDX Splice Modules, and SDX MTP Cassettes in LC, SC, ST, and MTP connectivity. Fiber cable management for routing, storage, and protection shall accept tight-buffered fiber and backbone cables. Enclosures shall be constructed of 16-gauge steel with a powder-coated black finish and be mountable on a wall. An optional key/lock kit shall be available to lock the service side door or both service-side and customer-side doors. Page 1 of 3

tel 1-800-824-3005

tel +1-425-486-2222

appeng@leviton.com

www.leviton.com

Leviton Network Solutions 2222 - 222nd St. SE Bothell, WA 98021-4416

Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com

Europe

Canada T+1.514.954.1840

India / SAARC

T +971.4.886.4722

E infoindia@leviton.com

Caribbean T +1.954.593.1896 E pcservice@leviton.com

E infocaribbean@leviton.com Mexico

T +52.55.5082.1040

E lsamarketing@leviton.com

China

T +852.2774.9876 E infochina@leviton.com

Middle East & Africa **T**+971.4.886.4722 E Imeinfo@leviton.com

South Korea T+82.2.3273.9963 E infokorea@leviton.com

E infocolombia@leviton.com

Colombia

T +57.1.743.6045

FEATURES

- · Dual doors (service side and customer side) with slam latches for ease of access
- · Low-profile (depth), small-size enclosure minimizes protrusion from the wall
- · Large-size enclosure can be retrofitted in field for splice only enclosure (accepts up to 24 splice trays)
- Accepts SDX Adapter Plates, Splice Modules, MTP Cassettes, and Splice Trays for multiple solution capabilities
- Removable cable entry/exit grommets allow for pre-terminated fiber trunk install, cable protection, and minimizes dust buildup
- Constructed of 16-gauge steel for enhanced durability ٠
- Ground lug provided for added cable strain relief protection and grounding of armored cable
- Optional cable strain-relief mounting kit (installed on service side) protects incoming fiber cable
- Optional key/lock kit secures service-side door or service-side and customer-side doors
- Optional HDX-to-SDX conversion adapter bracket accepts HDX Adapter Plates and HDX Cassettes

DESIGN CONSIDERATIONS

- Enclosures are sold empty (unloaded)
- Capable of storing up to three meters of 900 µm tight-buffered . fiber per adapter
- Enclosures are powder-coated black (custom white available)
- Enclosures include an accessory kit consisting of VELCRO brand cable ties, mounting screws, cable managers, port ID labels, blank plates and CAM lock (for splice-only enclosure)

STANDARDS COMPLIANCE & FIBER DENSITY

Meets or exceeds all ANSI/TIA-568.3-D requirements

PHYSICAL SPECIFICATIONS

Dimensions:

See page two

Materials:

- Enclosures: 16-gauge steel, powder-coated black, white logo
- Cable entry/exit grommet: santoprene

		FIBER DENSITY				
Size	# of SDX Components	MTP (12f / 24f)	LC	sc	ST	
Small	2	192 / 384	48	24	24	
Medium	4	384 / 768	96	48	48	
Large	12	1,152 / 2,304	288	144	144	

Copyright © 2017 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

E customerservice@brand-rex.com

T+44.0.1592.772124

COMPONENT SPECIFICATIONS 5Wxxx-xxC




WARRANTY INFORMATION

For a copy of Leviton product warranties, visit www.leviton.com/warranty.

ELECTRONIC FILES

For CAD files, typical specs, or technical drawings (.DXF, .DWG), visit www.leviton.com.


Small Wall-Mount Enclosure



Copyright © 2017 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.



HDX-to-SDX Adapter Bracket



SPLICE TRAY CAPACITY CHART								
	Heat Shrink (Plastic Holders)	Bare Fusion	Small	Medium	Large			
Metal Splice Tray (0.25" Height)								
12-Fiber Mini, 4" x 7"	T47HS-P06	T47BF-P06	2	4	12			
12-Fiber Mini, w/ standoff, 4" x 7"	5T000-00T	—	2	4	12			
72-Fiber High Density, 6" x 10"	T6XRB-40Q		2	4	12/24			
Injection Molded Splice Tray (Mini - 0.39" Height, High-Density - 0.43" Height)								

OPT-X® SDX WALL-MOUNT ENCLOSURES & ACCESSORIES

Description	Part No.
Small Enclosure, empty with dual door, no lock	5WSML-02C*
Medium Enclosure, empty with dual door, no lock	5WMED-04C*
Large Enclosure, empty with dual door, no lock	5WLRG-12C*
Lock and key	5L000-L0K
Splice tray mounting hardware kit	SPLMT-HKT
Cable clamp kit (single grommet)	5RCMP-KIT
Cable clamp kit (multiple cable grommets)	5RCMP-KT2
HDX-to-SDX Adapter Bracket	HDXAD-ACC

* Contact Inside Sales for white colored option. Minimum order quantities and lead time may apply.



Leviton Network Solutions 2222 - 222nd St. SE	
Bothell, WA 98021-4416 tel 1-800-824-3005	

tel +1-425-486-2222

www.leviton.com

appeng@leviton.com

Asia / Pacific T +1.631.812.6228 E infoasean@leviton.com

Europe

India / SAARC **T** +44.0.1592.772124 T +971.4.886.4722

T +1.514.954.1840 E pcservice@leviton.com

E infoindia@leviton.com

Canada

Caribbean T +1.954.593.1896 E infocaribbean@leviton.com

Mexico T +52.55.5082.1040 E lsamarketing@leviton.com Middle East & Africa **T** +971.4.886.4722 E Imeinfo@leviton.com

E infochina@leviton.com

T +852.2774.9876

China

South Korea T +82.2.3273.9963 E infokorea@leviton.com

E infocolombia@leviton.com

Colombia

T +57.1.743.6045

Copyright © 2017 Leviton Manufacturing Co., Inc. All rights reserved. Subject to change without notice.

E customerservice@brand-rex.com

