

USB 3.0 SuperSpeed to SATA III Adapter Cable with UASP, 2.5 in. SATA Hard Drives, White

MODEL NUMBER: **U338-06N-SATA-W**



Description

The U338-06N-SATA-W USB 3.0 SuperSpeed to SATA III Adapter Cable connects a 2.5-inch SATA hard disk drive (HDD) or solid state drive (SSD) to an available USB port on your laptop or computer. This lets you back up important data, retrieve data from an old hard drive, or store information on an external drive that you can take with you to another computer.

This adapter cable supports USB 3.0 data transfer rates up to 5 Gbps. Its UASP (USB Attached SCSI Protocol) feature reduces latency and allows the cable to perform up to 70% faster when connected to a UASP-enabled host controller.

Perfect for storing and sharing large files, such as music and video files, the U338-06N-SATA-W is compatible with SATA drives up to 4 TB. Just insert the drive into the 22-pin SATA connector, and attach the built-in USB 3.0 cable to your computer.

The U338-06N-SATA-W accepts SATA III (6 Gbps), SATA II (3 Gbps) and SATA I (1.5 Gbps) drives, as well as USB 2.0 (480 Mbps) and USB 1.1 (12 Mbps) transfer speeds. It supports LBA-48 bit (Logical Block Addressing) and USB Mass Storage Class Bulk-Only Transport. No software, drivers or external power supply is required. Compatible with all USB-enabled operating systems.

Features

Quickly Connects a SATA Drive to Your Computer's USB Port

- Recommended for backing up, retrieving and storing large data files
- Supports USB 3.0 data transfer rates up to 5 Gbps
- Features UASP for performance up to 70% faster when connected to UASP-enabled host controller

Compatible with 2.5 in. SATA HDDs and SSDs Up to 4 TB

- Accepts SATA III, SATA II and SATA I drives

Highlights

- Supports USB 3.0 data transfer rates up to 5 Gbps
- Works up to 70% faster when connected to UASP host controller
- Compatible with SATA HDDs and SSDs up to 4 TB
- Plug-and-play—no external power supply required
- Compatible with all USB-enabled operating systems

Applications

- Formatting hard drives, File Transfers, or External Storage

System Requirements

- Any USB-enabled operating system
- Available USB port (USB 3.0 required to achieve USB 3.0 speeds)
- 2.5 in. SATA drive
- UASP-enabled host controller required for UASP performance

Package Includes

- U338-06N-SATA-W USB 3.0 SuperSpeed to SATA III Adapter Cable, White



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Backward compatible with previous USB generations
- Supports LBA-48 bit and USB Mass Storage Class Bulk-Only Transport

Easy to Use

- Plug-and-play—no software, drivers or external power supply needed
- Compatible with all USB-enabled operating systems

Specifications

PHYSICAL	
Color	White
ENVIRONMENTAL	
Operating Temperature Range	50 TO 122 F (10 TO 50 C)
Storage Temperature Range	32 TO 149 F (0 TO 65 C)
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	22 PIN SATA + POWER (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>