

OUTSOURCE™

POWER OVER ETHERNET MIDSPAN INJECTOR



Compact, midspan injectors that deliver reliable POE for IP cameras and devices

Delivers enhanced POE to all 802.3af/802.3at POE and POE Plus devices. OUTSOURCE & OUTSOURCE Plus automatically detect compatible devices.

Delivers reliable remote power to IP cameras including PTZ devices

Designed for straightforward installation for high power devices

Safety assured as POE is only enabled to compliant equipment

Compact, wall-mountable unit

Integrated overload protection

Sealed, fanless design for reliability



TECHNICAL SPECIFICATION

OUTSOURCE™ / PLUS™

POWER		
Input Voltage	90 to 264V AC, 47 to 63Hz	
Maximum current	0.55A	
FORWARDED POE POWER		
OUTSOURCE	19.6 watts	(Output voltage 56V)
OUTSOURCE Plus	30 watts	(Output voltage 56V)
	Overload and short-circuit protection	
	POE output on data pairs (1 & 2, 3 & 6)	
POE STANDARDS		
OUTSOURCE	IEEE 802.3af POE	
OUTSOURCE Plus	IEEE 802.3at POE	
ETHERNET INTERFACE		
	RJ45 Data IN port	
	RJ45 Data & POE OUT port	
	10/100/1000 Base-T compatible	
LEDS		
Status indicators	Solid Green LED	POE load detected, POE output ON
	Blinking Green LED	Power on, no POE load
	Blinking Red/Green LED	Invalid load connected
	Blinking Red LED	Fault condition
PHYSICAL / ENVIRONMENTAL		
Dimensions	L 163mm (inc mounting holes) W 65mm H 36mm	
Weight	200g (7.06oz)	
Mounting	Integral wall-mount lugs	
Operating temperature	0°C to +40°C (32°F to 104°F)	
Relative humidity	5% to 90% non-condensing	
Compliance	CE, FCC, RoHS	
PRODUCT CODES		
	VOR-OS	OUTSOURCE POE Injector
	VOR-OSP	OUTSOURCE Plus POE Plus Injector



OUTSOURCE PLUS



OUTSOURCE



veracity

Americas & Asia Sales :

Veracity USA Inc.
65 Harristown Road
Glen Rock
NJ 07452

USA
Tel: 1-800-679-1590
Fax: 1-800-679-0714
www.veracityglobal.com
sales@veracityusa.com

EMEA Sales :

Veracity UK Ltd
Prestwick International Aerospace Park
4 Dow Road
Prestwick
KA9 2TU
UK
Tel +44 (0) 1292 264967
Fax +44 (0) 845 528 1081
www.veracityglobal.com
sales@veracityuk.com