



18v LXT® Lithium-Ion Brushless Cordless 4-1/2" / 5" Paddle Switch Cut-Off/Angle Grinder Kit, with Electric Brake (5.0Ah) Model XAG11T

Electric Brake and Electronic Torque Control for Increased Operator Convenience



PRODUCTIVITY

Electric brake stops the grinding or cut-off wheel in 2 seconds or less for maximum productivity



CONTROL

Electronic Torque Control turns the motor off if rotation speed suddenly slows or stops



INNOVATION

Automatic Speed Change™ technology adjusts speed and torque during operation for optimum performance



POWER

BL™ Motor delivers 8,500 RPM

LXT® BRUSHLESS



Also Available as a Bare Tool
Model XAG11Z

FEATURES

- The BL™ Brushless Motor eliminates carbon brushes, enabling the BL™ Motor to run cooler and more efficiently for longer life; delivers 8,500 RPM
- Efficient BL™ Brushless motor is electronically controlled to optimize battery energy use for up to 50% longer run time per charge
- The electronically-controlled BL™ Brushless Motor efficiently uses energy to match torque and RPM to the changing demands of the application
- Compact and ergonomic design at only 14-1/4" long
- Weighs only 5.8 lbs. with battery for reduced operator fatigue
- Rubberized soft grip provides increased comfort on the job
- 3-stage L.E.D. gauge indicates battery charge level
- Extreme Protection Technology (XPT™) is engineered for improved dust and water resistance for operation in harsh conditions

SPECIFICATIONS

Wheel Diameter	5"
Battery	18V LXT® Lithium-Ion
No Load Speed	8,500 RPM
Spindle Thread	5/8" - 11 UNC
Lock On Switch	No
Lock-Off	Yes
Grinder Switch Type	Body grip/paddle
Overall Length	14-1/4"
Net Weight (with battery)	5.8 lbs.
UPC Code (XAG11T)	088381-849289
UPC Code (XAG11Z)	088381-814942

STANDARD EQUIPMENT

XAG11T

- (2) 18V LXT® Lithium-Ion 5.0Ah Batteries (BL1850B)
- 18V LXT® Lithium-Ion Rapid Optimum Charger (DC18RC)
- 5" Tool-Less Wheel Guard (123145-8)
- 5" Cut-Off Wheel Guard (122911-0)
- 5" X 1/4" X 7/8" Inox Grinding Wheel, 36 Grit (A-95962)
- 5" Ultra Thin Cut-Off Wheel, Stainless (B-46165)
- Side Handle
- 14" Contractor Tool Bag (831253-8)

XAG11Z

- 5" Tool-Less Wheel Guard (123145-8)
- 5" Cut-Off Wheel Guard (122911-0)
- 5" X 1/4" X 7/8" Inox Grinding Wheel, 36 Grit (A-95962)
- 5" Ultra Thin Cut-Off Wheel, Stainless (B-46165)
- Side Handle

OPTIONAL ACCESSORIES

- 4-1/2" - 5" Dust Extracting Surface Grinding Shroud (195236-5)
- 5" Dust Extracting Cutting Guard (193794-5)
- 5" Dust Extracting Tuck Point Guard (196846-1)
- 18V X2 LXT® Lithium-Ion (36V) Cordless/Corded 2.1 Gallon HEPA Filter Dry Vacuum, Tool Only (XCV04Z)
- 12 Gallon Xtract Vac® Wet/Dry Vacuum/Dust Extractor (VC4710)