



American Dynamics

From Tyco Security Products

victor Workstations

Features That Make a Difference:

- Affordable, entry-level workstations
- Two chassis options
- Intel® Xeon processors
- NVIDIA® Quadro graphics adapters
- RAID storage option
- Windows operating system included
- Three-year limited warranty
- NBD (Next Business Day) On-site Service



Affordable, Entry-level Workstations

For about the price of a desktop PC, choose one of two compact sizes, each of which delivers true workstation performance.

Compact Minitower

The workstation features a convenient hand hold for easy deployment and positioning.

victor Client

The small Form Factor (SFF) design does not require a power pack, which simplifies installation and saves space.

Fast, Stable Processing

Intel Xeon processors ensure both speed and reliable performance.

Powerful Graphics Capabilities

NVIDIA Quadro professional-grade discrete graphics adapters are included with each workstation to improve video performance and rendering.

Rapid Data Transfer



Each workstation features two front-mounted USB 3.0 ports to enable fast data transfer and easy connectivity to external media and accessories.

Operating Systems Included

A Windows® 7 Professional 64-Bit Operating System is included with each workstation.

Superior Warranty and Support Service

Each application server is backed by a three-year limited warranty. Next Business Day On-Site Service is offered with every model.

Hardware	victor Minitower	victor Client
Part #	VIC-TWRSVR1	VIC-CL1
		
form factor	Compact Minitower	SFF
Description	Compact, entry-level server	Compact, entry-level workstation
Processors	Intel Xeon E3	Intel Core i5
Operating Systems	Windows 7 Professional 64-Bit	Windows 7 Professional 64-Bit
Memory ¹	16 GB (2 x 8 GB)	16 GB (2 x 8 GB)
Graphics	NVIDIA Quadro K620	NVIDIA Quadro K620
Hard Drives	3.5" serial ATA	3.5" serial ATA
Storage ¹	1 TB	1 TB
Network Interface	1GbE	1GbE
Dimensions (W x H x D)	17.5cm x 36.0cm x 43.5cm (6.89in x 14.1in x 17.13in)	9.3cm x 29.0cm x 31.2cm (3.6in x 11.4in x 12.28in)
Power Supplies	305W	255W
RAID	1	No
Emissions	EN55022 Class B	EN55022 Class B
Immunity	EN55024	EN55024
Safety	EN/IEC60950-1	EN/IEC60950-1
Environmental	RoHS	RoHS
Warranty and Support Services	Three-year limited warranty plus onsite service	Three-year limited warranty plus onsite service
Max BTU	1245 BTU/hr	989 BTU/hr
DVD Drive	Yes	No

¹ Actual capacity varies depending on operating environment and other factors and will be less.

Ordering Information

Model Numbers	Description
VIC-TWRSVR1	victor Minitower, Windows 7 Professional, NVIDIA Graphics Card
VIC-CL1	victor Client PC, SFF, Windows 7 Professional, NVIDIA Graphics Card

Related Products



victor Unified Client



VideoEdge NVRs and Hybrids



illustra IP cameras



Software House C•CURE 9000 Access Control

Approvals



www.americandynamics.net