


# Double Door Latch. Eliminate the elbow catch.

**Eliminates the need for an elbow catch, or other devices, and allows hardware to be installed out of the way.**

- ◆ No need to reach inside cabinet to release elbow catch
- ◆ Doors can be closed in any order
- ◆ Low profile Latch mechanism reduces product footprint inside cabinet
- ◆ Requires use of a single lock (sold separately)
- ◆ Allows two or three point locking for standard or wardrobe style double door cabinets when used with a lock
- ◆ Easy to install and use
- ◆ Exceeds pull force above 150lbs



	Top Mount Kit STOCK LOCKS Part numbers	Bottom Mount Kit STOCK LOCKS Part numbers
Lock Placement		
Lock on Right Door	D200DL-BLK	D300DL-BLK
Lock on Left Door	D300DL-BLK	D200DL-BLK

*Also available in white finish.*

Only from **CompX Security Products**, the one-stop cabinet lock supplier.

Call **864-297-6655** or visit **compX.com** to learn more.

# Double Door Latch. Eliminate the elbow catch.

## How it works:

Eliminates the need for an elbow catch, or other devices, and allows hardware to be installed out of the way.

### Example: D200DL-BLK with lock (sold separately) on right hand door

The lock is mounted on the right hand door. Inside the right hand door, install the activator; on the non-locking door, install the catch.


The latch should be installed inside top of cabinet. The activator pushes the bolt on the latch to the other side to engage the catch. The bolt on the catch side is spring-loaded, allowing the doors to be **closed** in any order.

Turn the key to lock the other door; both doors are now secure. The locking door must be opened first to disengage the bolt in the latch – the bolt will slide back, allowing the non-locking door (with the catch) to open.



Watch the Double Door Latch video at [compX.com/ddl](http://compX.com/ddl)

### Kits contain one each: latch, activator and catch



## How to order:

- 1: Determine location of lock – right hand or left hand
- 2: Decide where latch is needed – top or bottom mount
- 3: Choose color – black or white

Each kit comes with complete installation instructions. Instructions are also available online: [compX.com/instructions](http://compX.com/instructions)

3D engineering models are also available online: [compX.com/models](http://compX.com/models)

### STOCK LOCKS Part numbers

Lock Placement	Top Mount Kit	Bottom Mount Kit
Lock on Right Door	<b>D200DL-BLK</b> Black Finish	<b>D300DL-BLK</b> Black Finish
	<b>D200DL-WHT</b> White Finish	<b>D300DL-WHT</b> White Finish
Lock on Left Door	<b>D300DL-BLK</b> Black Finish	<b>D200DL-BLK</b> Black Finish
	<b>D300DL-WHT</b> White Finish	<b>D200DL-WHT</b> White Finish

CATCH ON THE NON-LOCKING DOOR ACTS AS A SLAM LATCH AND DOES NOT REQUIRE REACHING INTO THE CABINET

SIGNIFICANT ENGAGEMENT BETWEEN THE CATCH AND LATCH INCREASES SECURITY

(D300DL-BLK SHOWN)

CATCH

LATCH

ACTIVATOR

Note: For cabinets taller than 48" it is recommended to use both top and bottom mount latches.