

DOOR LOCKS



290 SERIES



240 SERIES

Application - Surface mounted lock for locking doors.

Operation - 180° key rotation, CCW to lock, key removable in both locked and unlocked positions.

Keying - Order lock plug separately, see page 2.

Packaging - Housing is black, toughened nylon. Cylinder is unplated. Cams are zinc plated. Case quantity 25.

Part No.	Type	Cam Setback	Cam Extension*	Cam Throw	Case Quantity
C240CB	240	3/32"	15/16"	1/2"	25
C241CB	241	3/32"	1-3/8"	1/2"	25
C242CB	242	3/32"	2-5/8"	1/2"	25
C244CB	244	19/32"	1-1/2"	1/2"	25
C245CB	245	7/8"	1-1/2"	1/2"	25
C290CB	290	9/32"	13/16"	3/8"	25
C291CB	291	9/32"	1-1/4"	3/8"	25

* Measured from center of cylinder to tip of cam in unlocked position

DRAWER LOCKS



280 SERIES



230 SERIES

Application - Surface mounted lock for locking drawers.

Operation - 180° key rotation, CCW to lock, key removable in both locked and unlocked positions.


Keying - Order lock plug separately, see page 2.

Packaging - Cylinder is black, toughened nylon. Cylinder is unplated. Cams are zinc plated. Case quantity 25.

Part No.	Type	Cam Setback	Cam Extension*	Cam Throw	Case Quantity
C230CB	230	3/32"	15/16"	1/2"	25
C231CB	231	3/32"	1-3/8"	1/2"	25
C232CB	232	3/32"	2-5/8"	1/2"	25
C234CB	234	19/32"	1-1/2"	1/2"	25
C235CB	235	7/8"	1-1/2"	1/2"	25
C280CB	280	9/32"	13/16"	3/8"	25
C281CB	281	9/32"	1-1/4"	3/8"	25

* Measured from center of cylinder to tip of cam in unlocked position

GLASS DOOR LOCKS



Keying - Order lock plug separately, see page 2.

Application - Swing style doors.

Operation - 90° rotation. CCW to lock. Requires 7/8" Dia. hole bored in glass centered 7/8" from edge.

Glass Door Lock Bore Through Style Mounts In Glass Doors Up To 3/8" Thick

Part No.	Finish	Version	Cam Setback	Case Quantity
C301CB-14A	Polished Nickel	Horizontal Mount	15/16"	10
C305CB-3	Polished Brass	Horizontal Mount	15/16"	10
C307CB-15	Satin Nickel	Horizontal Mount	15/16"	10
C311CB-14A	Polished Nickel	Vertical Mount	15/16"	10
C315CB-3	Polished Brass	Vertical Mount	15/16"	10
C317CB-15	Satin Nickel	Vertical Mount	15/16"	10

Glass Door Lock Compression Mount Style Mounts On Glass Door 1/4" - 5/16" Thick

Application - Swing style doors.

Operation - 180° rotation. Lock slips onto edge of glass door at any location. Works with C185SP-19 strike plate.

Part No.	Finish	Version	Cam Throw	Case Quantity
C351CB-14A	Polished Nickel	Horizontal Mount	1/2"	10
C355CB-3	Polished Brass	Horizontal Mount	1/2"	10
C357CB-15	Satin Nickel	Horizontal Mount	1/2"	10
C361CB-14A	Polished Nickel	Vertical Mount	1/2"	10
C365CB-3	Polished Brass	Vertical Mount	1/2"	10
C367CB-15	Satin Nickel	Vertical Mount	1/2"	10


Glass Door Lock Double Door Style Mounts On Glass Door 1/4" - 5/16" Thick

Application - Double swing style doors.

Operation - 180° rotation. Lock slips onto edge of glass door. Tab provides stop for opposing door. Works with C185SP-19 Strike Plate.

Part No.	Finish	Version	Cam Throw	Case Quantity
C371CB-14A	Polished Nickel	Vertical Mount	1/2"	10
C375CB-3	Polished Brass	Vertical Mount	1/2"	10
C377CB-15	Satin Nickel	Vertical Mount	1/2"	10

CAM LOCK KITS C165CB, C168CB, C169CB



Application - Universal type lock for either doors or drawers. Each kit contains a variety of easily switched cams to accommodate most locking situations.

Operation - 90° & 180° cam rotation, CCW to lock.

Keying - Order lock plug separately, see page 2.

Packaging - Cylinder supplied with two straight and bent cams. Bent cams have setback of 15/32". Cylinder is unplated. Case quantity 25.

These Kits will Replace the Following Timberline Cam Locks:

C165CB 90° Rotation	C168CB 180° Rotation (Horizontal)	C169CB 180° Rotation (Vertical)
CB-080 CB-083 CB-084 CB-085 CB-087 CB-088 CB-090 CB-093 CB-094 CB-095 CB-097 CB-098	CB-180 CB-183 CB-184 CB-185 CB-187 CB-188	CB-190 CB-193 CB-194 CB-195 CB-197 CB-198

TWO DRAWER SIDE GANG LOCK D270CB



Application - Two drawer gang lock for locking two pedestal drawers with a single lock. Lock mounts on side of cabinet.

Operation - 180° key rotation, CCW to lock, key removable in both locked and unlocked positions.

Keying - Order lock plug separately, see page 2.

Packaging - Housing supplied with two C500DC-19 Drawer Clips. Case quantity 25.