

HDMI to DisplayPort Active Converter 4K with USB Power, HDMI to DisplayPort (M/F), 4096 x 2160/4K x 2K @ 30 Hz, 6 in.

MODEL NUMBER: **P130-06N-DP-V2**



Description

The P130-06N-DP-V2 HDMI to DisplayPort Active Converter 4K (M/F) connects an HDMI audio/video source, such as a computer or Blu-ray™ player, to a 4K-enabled DisplayPort monitor or projector. With a male HDMI input and female DisplayPort output, this converter lets you use your existing DisplayPort display and saves you time, money and effort of upgrading to a new HDMI display. It also connects DVI or mini-DVI sources to a DisplayPort monitor using adapter cables, such as Tripp Lite's P566-Series DVI to HDMI cables (sold separately).

Ideal for home theater setups, digital signage, trade show presentations and classroom lectures, the HDMI to DisplayPort adapter supports video resolutions up to 4096 x 2160 (4K x 2K) at 30 Hz. It also supports 7.1-channel surround sound, and is compliant with HDCP 1.3 and DisplayPort 1.2a. It transmits EDID information to ensure optimal display compatibility.

This six-inch cable is plug-and-play with no software or drivers needed. If more power is required, connect the unit's built-in USB-A plug to a USB source. Corrosion-resistant gold-plated connectors and contacts provide maximum conductivity and minimize data loss. Integral strain relief gives the cable extra flexibility, reduces stress, and helps the cable and connectors move freely without cracking.

The P130-06N-DP-V2 fits easily in a briefcase, backpack or laptop bag for connecting on the go. DisplayPort and USB cables sold separately.

Features

Sends HDMI Audio/Video Signals to a 4K DisplayPort Monitor or Projector

- Ideal for home theater setups, digital signage, trade show presentations and classroom lectures
- Male HDMI and female DisplayPort connectors
- Also connects DVI or mini-DVI source using adapter cables, such as Tripp Lite's P566-Series (sold separately)
- Built-in USB plug provides power if needed

Vibrant Audio/Video Quality

Highlights

- Active converter works with all HDMI sources
- Supports video resolutions up to 4096 x 2160 (4K x 2K) @ 30 Hz
- Supports 7.1-channel surround sound
- Transmits EDID info to ensure optimal display compatibility
- Compliant with HDCP 1.3 and DisplayPort 1.2a

System Requirements

- Computer, Blu-ray player or other source with HDMI output
- Monitor or other display with DisplayPort input

Package Includes

- P130-06N-DP-V2 HDMI to DisplayPort Active Converter 4K (M/F)
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

- Supports video resolutions up to 4096 x 2160 (4K x 2K) @ 30 Hz
- Supports 7.1-channel surround sound
- Transmits EDID info to ensure optimal display compatibility

Premium Construction for Top Signal Transfer

- Gold-plated connectors and contacts for maximum conductivity and minimum data loss
- Integral strain relief reduces stress and adds flexibility
- Compliant with HDCP 1.3 and DisplayPort 1.2a
- Fits easily into briefcase, backpack or laptop bag
- Plug-and-play—no software or drivers necessary

Specifications

INPUT	
Cable Length (ft.)	0.5
Cable Length (in.)	6
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (FEMALE); USB A (FEMALE)
Side B - Connector 1	HDMI (MALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>