


LASTS
10X
LONGER



PRECISION-FIT TIP
prevents "cam-out"
and stripping



XTREME TORSION TECHNOLOGY
for high torque applications

HIGH QUALITY STEEL
for extra strength

Learn More makitatools.com/ImpactGold

Impact GOLD® Bit Sets

Description

Part

NEW 38-Pc. Torsion Bit Set

B-52370

- Includes:
- (2) #2 Phillips / #2 Square 2-1/2" Double-Ended Power Bit
 - (2) #2 Phillips / #25 Torx® 2-1/2" Double-Ended Power Bit
 - (1) #2 Phillips / #30 Torx® 2-1/2" Double-Ended Power Bit
 - (1) 1/4" Detachable Nutsetter
 - (1) 5/16" Detachable Nutsetter
 - (1) 3/8" Detachable Nutsetter
 - (1) Detachable Nutsetter Adapter
 - (1) 1/4" Socket Adapter
 - (1) Mag Boost
 - (1) Torsion Bit Holder

- (2) #1 1" Phillips Insert Bit
- (8) #2 1" Phillips Insert Bit
- (2) #3 1" Phillips Insert Bit
- (1) #1 1" Square Insert Bit
- (3) #2 1" Square Insert Bit
- (1) #3 1" Square Insert Bit
- (1) #10 1" Torx® Insert Bit
- (1) #15 1" Torx® Insert Bit
- (2) #20 1" Torx® Insert Bit
- (3) #25 1" Torx® Insert Bit
- (2) #30 1" Torx® Insert Bit



Description

Part

NEW 26-Pc. Torsion Bit Set

B-46919

- Includes:
- (1) #2 2-1/2" Phillips Double-Ended Power Bit
 - (1) #3 2-1/2" Phillips Double-Ended Power Bit
 - (1) Mag Boost
 - (1) 1/4" Magnetic Nutsetter
 - (1) 5/16" Magnetic Nutsetter
 - (1) Torsion Bit Holder
 - (2) #1 1" Phillips Insert Bit
 - (5) #2 1" Phillips Insert Bit
 - (3) #3 1" Phillips Insert Bit
 - (1) #1 Square Insert Bit

- (2) #2 Square Insert Bit
- (1) #3 Square Insert Bit
- (1) #15 1" Torx® Insert Bit
- (1) #20 1" Torx® Insert Bit
- (2) #25 1" Torx® Insert Bit
- (1) #27 1" Torx® Insert Bit
- (1) #30 1" Torx® Insert Bit



Description

Part

21-Pc. Ultra-Magnetic Insert Bit Set

B-31893

- Includes:
- (1) Ultra Magnetic Insert Bit Holder
 - (1) #1 1" Phillips Insert Bit
 - (13) #2 1" Phillips Insert Bit
 - (1) #3 1" Phillips Insert Bit
 - (1) #2 1" Square Insert Bit
 - (1) #3 1" Square Insert Bit
 - (1) #15 1" Torx® Insert Bit
 - (1) #20 1" Torx® Insert Bit
 - (1) #25 1" Torx® Insert Bit



Description

Part

11-Pc. Torsion Magnetic Insert Bit Set

B-35112

- Includes:
- (1) Torsion Magnetic Insert Bit Holder
 - (10) #2 1" Phillips Insert Bit



Description

Part

7-Pc. Double-Ended Power Bits with Mag Boost

B-44987

- Includes:
- (1) Mag Boost
 - (3) #2 2-1/2" Phillips Double-Ended Power Bit
 - (2) #2 3-1/2" Phillips Double-Ended Power Bit
 - (1) #2 6" Phillips Double-Ended Power Bit



Double-Ended Power Bits

LASTS
20X
LONGER



HIGH QUALITY STEEL for extra strength

Description

Length

Qty./Pkg.

Part

Phillips Double-Ended Power Bit

| | | | |
|----|--------|---|---------|
| #1 | 2-1/2" | 3 | B-39578 |
| #2 | 2-1/2" | 3 | B-39584 |
| #3 | 2-1/2" | 3 | B-39590 |
| #1 | 3-1/2" | 1 | B-39609 |
| #2 | 3-1/2" | 1 | B-39615 |
| #3 | 3-1/2" | 1 | B-39621 |
| #2 | 6" | 1 | B-39637 |

- One bit with two magnetic tips for quick bit changes, last 20x longer than standard power bits
- Engineered with Xtreme Torsion Technology to handle the high torque of leading impact drivers
- Precision-fit tip prevents "cam-out" and stripping
- Designed exclusively for high-torque impact drivers



Description

Part

NEW 3-Pc. 2-1/2" Square Double-Ended Power Bit Sets

B-49600

- Includes:
- (1) Square #1 Double-Ended Power Bit
 - (1) Square #2 Double-Ended Power Bit
 - (1) Square #3 Double-Ended Power Bit



NEW 3-Pc. 2-1/2" Torx® Double-Ended Power Bit Sets

B-49616

- Includes:
- (1) #15 Torx® Double-Ended Power Bit
 - (1) #20 Torx® Double-Ended Power Bit
 - (1) #25 Torx® Double-Ended Power Bit



NEW 3-Pc. Combination 2-1/2" Double-Ended Power Bit Sets

B-49622

- Includes:
- (1) #2 Phillips / #2 Square Double-Ended Power Bit
 - (1) #2 Phillips / #25 Torx® Double-Ended Power Bit
 - (1) #2 Square / #25 Torx® Double-Ended Power Bit



Insert Bits

| Description | Length | Application | Qty./Pkg. | Part # |
|----------------------------|--------|--|-----------|---------|
| Phillips Insert Bit | #1 1" | Ideal for driving screws in a wide variety of heavy-duty fastening applications including deck building, framing and installing plywood subfloor | 4 | B-34936 |
| | #2 1" | | 4 | B-34942 |
| | #2 1" | | 15 | B-34958 |
| | #2 1" | | 100 | B-42569 |
| Torx® Insert Bit | #3 1" | | 4 | B-34964 |
| | #10 1" | | 2 | B-44644 |
| | #15 1" | | 2 | B-44650 |
| | #20 1" | | 2 | B-44666 |
| | #25 1" | | 2 | B-44672 |
| | #25 1" | | 25 | B-44731 |
| | #27 1" | | 2 | B-44688 |
| Square Insert Bit | #30 1" | | 2 | B-44694 |
| | #1 1" | | 2 | B-44703 |
| | #2 1" | | 2 | B-44719 |
| | #2 1" | | 25 | B-44747 |
| | #3 1" | | 2 | B-44725 |

- Engineered with Xtreme Torsion Technology to handle the high torque of leading impact drivers
- Precision-fit tip prevents "cam-out" and stripping
- Lasts up to 10X longer than standard insert bits
- Combine with an Impact GOLD® bit holder to last up to 15X longer than standard insert bits

Insert Bit Holders

| Description | Length | Qty./Pkg. | Part # |
|--|--------|-----------|---------|
| Ultra Magnetic Torsion Insert Bit Holder | 2-3/4" | 1 | B-35097 |
| Torsion Magnetic Insert Bit Holder | 2-5/8" | 1 | B-35106 |

- Engineered with Xtreme Torsion Technology to handle the high torque of leading impact drivers
- Combine with an Impact GOLD® Insert Bit to last up to 15X longer than standard insert bits
- High-quality steel for extra strength
- Ideal for driving screws in a wide variety of heavy-duty fastening applications including deck building, framing and installing plywood subfloor

Mag Boost

| Description | Fits | Part # |
|------------------|---------------------|---------|
| Mag Boost | 1/4" hex power bits | B-44971 |


- Makes power bits magnetic
- 17X more magnetic than standard bits
- Great for holding screws to the end of the bit in tight or long reach situations
- Fits most brand 1/4" hex power bits

MAG BOOST
XTREME
HOLDING POWER

MAG BOOST
holds 100 standard ball bearings

NO MAG BOOST
holds only 6 standard ball bearings

17X
MORE MAGNETIC
THAN STANDARD BITS

**Nutsetters**


| Description | Size | Length | Qty./Pkg. | Part # |
|------------------|-------|--------|-----------|---------|
| Nutsetter | 5/16" | 1-7/8" | 1 | B-35047 |
| | 5/16" | 1-7/8" | 10 | B-42684 |
| | 3/8" | 1-7/8" | 1 | B-35053 |
| | 3/8" | 1-7/8" | 10 | B-42690 |
| | 7/16" | 1-7/8" | 1 | B-35069 |
| | 7/16" | 1-7/8" | 10 | B-42709 |

- The exclusive snap-ring is non-magnetic and provides the holding power of standard magnetic nutsetters without the drawback of metal debris build-up
- High-quality steel for extra strength
- Ideal for driving hex head nuts and screws in a wide variety of applications

GRIP-IT™ NUTSETTER

Impact GOLD®

STANDARD MAGNETIC



Non-magnetic ring eliminates debris build-up



Collects debris and obstructs proper fit

**Socket Adapters and Socket Sets**

| Description | Drive | Shank | Part # |
|-----------------------|-------|----------|---------|
| Socket Adapter | 3/8" | 1/4" Hex | B-35075 |
| | 1/2" | 1/4" Hex | B-35081 |

- Socket adapter tilts up to 15° for work in tight spaces
- Also works in the straight position for increased versatility
- High-quality steel for extra strength
- Allows the use of square drive impact sockets with an impact driver
- Ideal for a wide variety of fastening applications

| Description | Part # |
|-------------|--------|
|-------------|--------|

Socket Sets

9-Pc. 3/8" Drive Impact Socket Set w/ 15° Tilt Socket Adapter
Includes: 3/8" Drive x 1/4" Socket Adapter, 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16" and 3/4" Impact Sockets

B-34833



NEW 9-Pc. 3/8" Drive Metric Socket Set w/ 15° Tilt Socket Adapter
Includes: 3/8" Drive x 1/4" Socket Adapter, 8mm, 10mm, 12 mm, 13mm, 14mm, 15mm, 17mm and 18mm Impact Sockets

B-49862

IMPACT SOCKET ADAPTER **TILTS 15°** for Tight Work Areas

