

# REINFORCED SPIRAL BANDS

**Description:** Small-sized abrasive cylinders internally reinforced with cotton cloth.

**Main features and benefits:** Compact design allows you to work even in very small spaces. Perfect adherence to backing and top-quality abrasive ensure long life. They should be used on expanders as with the same size as the spiral band (page 96).

**Recommended applications:** Finishing of moulded parts, internal surfaces of cylinders, pipes and drilled parts in general.

**Work surfaces:** Standard steel, stainless steel, nonferrous materials and alloys, plastic materials.



## SB

### ALUMINIUM OXIDE reinforced spiral bands

Aluminium oxide SB, X-weight backing.

diam./th.			P36	P50	P60	P80	P120	P150	P180
10x10	38.000	100				SB0004 •	SB0005	SB0006	SB0007
10x20	38.000	100		SB0016 •	SB0017 •	SB0018 •	SB0019 •	SB0020 •	SB0021
13x25	30.000	100	SB0029	SB0030	SB0031 •	SB0032 •	SB0033	SB0034 •	SB0035
15x10	26.000	100				SB0046	SB0047	SB0048	SB0049
15x30	26.000	100	SB0057 •	SB0058 •	SB0059 •	SB0060 •	SB0061 •	SB0062 •	SB0063
19x25	20.000	100	SB0071	SB0072	SB0073 •	SB0074 •	SB0075	SB0076	SB0077
22x20	17.000	100	SB0085 •	SB0086 •	SB0087 •	SB0088 •	SB0089	SB0090 •	SB0091
25x25	15.000	100	SB0099 •	SB0100	SB0101 •	SB0102 •	SB0103	SB0104 •	SB0105
30x20	13.000	100	SB0113	SB0114	SB0115 •	SB0116 •	SB0117	SB0118	SB0119
30x30	13.000	100	SB0127 •	SB0128 •	SB0129 •	SB0130 •	SB0131	SB0132 •	SB0133
38x25	10.000	100	SB0141	SB0142	SB0143	SB0144	SB0145	SB0146	SB0147
45x30	8.500	100	SB0155 •	SB0156 •	SB0157 •	SB0158 •	SB0159	SB0160 •	SB0161
51x25	7.500	100	SB0169	SB0170	SB0171 •	SB0172 •	SB0173	SB0174	SB0175
60x30	6.500	50	SB0183 •	SB0184	SB0185 •	SB0186 •	SB0187	SB0188	SB0189
75x30	5.000	50	SB0197	SB0198	SB0199	SB0200	SB0201	SB0202	SB0203
100x40	4.000	25	SB0211	SB0212	SB0213	SB0214	SB0215	SB0216	SB0217