



## Gauges & Accessories

### Organization



#### Storage Panel No. CARD-BP

Holds 40 code cards conveniently.  
Cards sold separately.



#### Instruction Manual Set

**No. CARD-B**  
for Blitz™ Series

**No. CARD-SB**

for Switch Blitz™ Series  
Includes Manual, Storage Panels  
for 150 cards and binder.

### Softie™ Brush



#### Softie™ Brush and Assembly

**No. 12SB**

Softie™ Brush  
Assembly

**No. TYX-3**

Softie™ Brush Only

It is important to de-burr newly cut keys to prevent obstructions in the lock. The **Softie™ Brush** is the only key machine brush made of Tylon-X (a unique space-age polymer). The carbide-impregnated material de-burrs faster and smoother, and **lasts 6 times longer than a wire brush**. The Softie™ Brush comes standard on the Tiger SHARK™, Blitz™, Switch Blitz™, Trace-A-Key® and all Speedex® machines. The Softie™ Brush Kit includes the brush, shield, pulley and installation hardware to add the Softie™ brush to standard models of the CodeMax®, 1200CM and older models of the Trace-A-Key® machines.

### Blitz™ Shoulder Gauge Safety Switch



#### Blitz™ Shoulder Gauge Safety Switch

**No. 1200C-SGS**

For 120VAC Machines

**No. 1200C-SGS240V**

For 240VAC Machines

The **Blitz™ Shoulder Gauge Safety Switch** is designed to protect the shoulder gauge from being accidentally damaged by the cutter. It prevents the cutter from spinning if the shoulder gauge is not positioned all the way down. When the Shoulder Gauge Safety Switch is not in its rest position turning on the machine will result in the safety switch relay disengaging the cutter motor's power. This will also happen if the gauge is moved from its rest position while the cutter motor is already on. This safety switch can easily be added to any 1200CM or Blitz™ machine manufactured from 1980 to 2004 (at which time it became standard equipment).

### 12-Volt Key Machine Conversion Kit



#### 12-Volt Key Machine Conversion Kit

**No. DC-12**

#### 12-Volt DC Motor Only

(Replacement motor for AC/DC equipped  
key machines.)

**No. DC-MOTOR**

The **12-Volt Key Machine Conversion Kit** allows for HPC's 9160MC and 9180MC Speedex® machines to be converted to 12VDC. By using the DC-12 kit you can operate your AC-powered duplicator in your van without the use of expensive inverters. It includes an in-line fuse for protection and a cigarette lighter adapter for plug-in convenience. The kit also includes: motor, frame, pulley, belt, 10 feet (3 meters) of 14-gauge wire, double-pole single-throw toggle switch.

Motor:	12VDC
Power:	40 oz.-inch torque rating, 3000 rpm with load 1/6 hp / 12 amps
Cutter RPM:	1000 rpm (by use of the pulley included)
Shaft:	3/8" (9.5mm) diameter, rotates within ball bearings
Frame:	Standard NEMA 48 configuration
For use with:	9160MC and 9180MC Speedex®