

6-Port USB 3.0 SuperSpeed Charging Hub - 2x USB 3.0, 4x USB 2.0, 1 charging port

MODEL NUMBER: U360-412



Description

Tripp Lite's U360-412 USB 3.0 Charging Hub plugs into a computer's USB 3.0 port and provides two USB 3.0 SuperSpeed peripheral ports, four USB 2.0 High-Speed peripheral ports, and one charging port for charging tablets such as an iPad. Two of the USB 2.0 ports have convenient top plugging, for thumb drive access. Dedicated 2AMP charging port supplies the extra amperage needed to charge tablets, which most USB hubs do not include. Plug-and-Play... no software or drivers required. Automatically switches to the highest speed supported by the peripheral. Windows (compatible with Windows 10) and Mac compatible.

Features

- USB 3.0 ports support 5Gbps transfer speeds when plugged into a USB 3.0 computer and peripheral
- USB 2.0 ports support High-Speed 480Mbps speeds
- Charging port provides 5V,2A for tablet (iPad) full battery charging
- USB 3.0 ports support up to 900mA per port
- USB 2.0 ports support up to 500mA per port
- The included external power supply provides 4A of power, to be shared between the hub ports (up to 2A for iPad charging port, up to 900mA per USB 3.0 port, up to 500mA per USB 2.0 port)
- Top mount ports for Thumb Drive connections
- Plug-and-Play
- No software or drivers required
- Windows (compatible with Windows 10) and Mac compatible
- Overcurrent protection
- LED power indicator light

Specifications

Highlights

- USB 3.0 Hub with two USB 3.0 SuperSpeed ports and four USB 2.0 High-Speed ports
- One dedicated port for Tablet charging (5V, 2A)
- USB 3.0 ports support up to 900mA per port
- USB 2.0 ports support up to 500mA per port
- Plug-and-Play - no software or drivers required

System Requirements

- USB 3.0 or 2.0 computer
- USB 3.0 or 2.0 peripherals

Package Includes

- USB 7-port Hub
- USB 3.0 A-B cable, 3ft
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.9A; Output: 5V, 4A)



OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.9A; Output: 5V, 4A
OUTPUT	
Charging Ports / Amps	(1) 2A
PHYSICAL	
Unit Dimensions (hwd / in.)	1 x 4 x 2.25
Unit Dimensions (hwd / cm)	2.54 x 10.16 x 5.72
Color	Black
CONNECTIONS	
Ports	6
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(2) USB 3.0 A (FEMALE)
Side B - Connector 2	(4) USB A (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>