

# Trilogy Ordering Information

## Choice of three standard Trilogy finishes



US3  
Polished Brass



US26D  
Satin Chrome



US10B  
Duronodic

## U.S. Handing options



00 Straight Lever



75 Regal Curved Lever



25 Turnpiece  
50 Knob available on  
DL1250/1350

## DL-WINDOWS Trilogy Software

Free Alarm Lock Trilogy Microsoft Windows-based software application, for programming, entering users, receiving audit trail from lock or used with ALDTMs to transfer data. Version 4.177 or higher, supports Trilogy Networkx, Wireless Keypads, Locks and ArchiTech series, and Trilogy standalone locks, with single database. Downloadable free at [www.alarmlock.com](http://www.alarmlock.com). For enterprise network software options, and real-time performance, see pg.15



## Trilogy audit trail and programming

### AL-IR1 Infrared Printer

Prints the event log and user code with hand-held convenience.



### AL-DTMIII Data Transfer Module

Module used to transfer program data from the PC to the lock and receive Audit Trail from the lock. Can transfer program data for up to 200 locks.



### AL-PRE2 Dual Function Reader/Enroller for Smart Cards or Prox IDs

Just tap the Smart Card or Prox ID device to the unit's faceplate to automatically enroll in DL-WINDOWS software database. (9V battery operation.)



### AL-PCI2U Lock / PC Interface (shown)


Interface cable interconnects lock and PC for data transfer with USB interface cable. (AL-PCI also includes DL-WINDOWS CD). Also available AL-PCI2 w/o USB.



## Remote Release Kit

### RR-TRILOGYKIT

Remote release kit for all Trilogy Cylindrical models includes the **RR-1BUTTON** for desk mount applications and **RR-RECEIVER** for installation inside the battery compartment of any cylindrical Trilogy lock (Simply connects to the 2 white remote release wires inside. Retrofits any existing cylindrical Trilogy manufactured since 1994.



Also available for Mortise and Exit Trim models, **RR-MORTISEKIT** and **RR-EXITTRIMKIT**, respectively. (Note: individual kit components, in blue, are also separately available.)

## Cylindrical Trilogys

DL 27 00 WP IC /26D -Y

### Model/Series:

DL27 = DL2700 Series  
DL28 = DL2800 Series  
DL30 = DL3000 Series  
DL32 = DL3200 Series  
DL52 = DL5300 Series  
PDL30 = PDL3000 Series  
PDL53 = PDL5300 Series

### Networkx Wireless:

DL100 PIN Series;  
PDL6100, 8200 PIN/Prox

### Trim:

00 = Lever  
75 = Regal Curved Lever

### Exterior/Interior Use:

For Exterior use of DL2700 & DL3000 only, order WP for weatherproof use. All other models are weatherproof as standard.

### Cylinder:

IC = Standard Interchangeable Core Prep for Best, Falcon, Arrow, KSP

(Note: No "IC" indicates standard K.O. cylinder.)

### Finish:

/3 = US3 Polished Brass  
/26D = US26D Satin Chrome  
/10B = Duronodic (Special Order)

### Special Order IC Prep:

-Y = Yale  
-M = Medeco  
-R = Sargent  
-C = Corbin/Russwin  
-S = Schlage

## Mortise Trilogys

DL 35 00 DB R /26D EX

### Model & Series:

DL35 = Trilogy T3 Mortise Series

### Networkx Wireless:

DL6500 PIN; PDL6500 PIN/Prox

### Trim:

00 = Standard Lever  
75 = Regal Curved Lever (U.S. Option Only)

### Lock Body:

DB = Dead Bolt  
CR = Class Room (U.S. Only)

### Handing:

Your Door -	Order -
Left Handed	L
Right Handed	R
Left Hand Reverse Bevel	R
Right Hand Reverse Bevel	L

### Finish:

/3 = US3 Polished Brass  
/26D = US26D Satin Chrome  
/10B = Duronodic (Special Order)

### European Model Suffix

Not Used For U.S. Models  
\*Note: Standard Lever for U.S. Models is Straight Lever.  
Standard Lever for European Models is Curved Tubular Lever

(Note: Trim is non-handed. Lock body is field reversible.)

## Trilogy Narrow Stile

DL1200/26D1

### Model Type

PDL = Prox/PIN  
DL = Digital PIN

### Trilogy Series

12 = 2700 Series  
13 = 3000 Series

### Trim

00 = Lever  
25 = Turnpiece  
50 = Knob  
75 = Regal lever

### Finish

/26D Satin Chrome  
/10B Duronodic  
/MS Metallic Silver  
/MB Metallic Bronze

### Mechanical Dead Latch

1 - Supports Adams Rite:  
4710, 4730, 4900 Series  
2 - Supports Adams Rite:  
4070, MS1850S,  
MS1850S-050, MS1950,  
MS1950-050  
3 - KIT Includes Adams Rite  
4900 with 1-1/8" backset,  
628 & 313 faceplate  
4 - KIT Includes Adams Rite  
4900 with 1-1/2" backset,  
628 & 313 faceplate

## Trilogy Exit

ETPDL- 1 R/ 26D V99

### Type:

PDL = Digital with Prox  
PL = Prox Only  
DL = No Prox

N = (suffix) Networkx Wireless

### Door Thickness:

1 = 1 3/4" + 1/8"  
2 = 2" to 2 3/4"  
3 = 3" to 4"

### Handle:

R = Regal  
S = Straight

### Finish:

/3 = US3 Polished Brass  
/26D = US26D Satin Chrome  
/10B = Duronodic (Special Order)

### OEM Trim

V99 = Von Duprin 99  
C50 = Corbin ED5000 & Yale  
D93 = Dorma 9300  
A38 = Arrow 3800  
S88 = Old Style Sargent  
N58 = New Style Sargent  
P11 = Precision 1100  
CR8 = Cal Royal 9800