# Door alarms: Advanced and multi-purpose



## PERSONS DURING AND AFTER SCHOOL HOURS **VOLATORS WILL BE PROSECUTED**

PG21MS Series surface-mount narrow stile door alarms.

### Ideal in schools, nursing homes, restaurants & theatres

#### Models PG21MS/PG21MB

- Two selectable arming modes -
  - 1. Always armed mode when key is turned counter clockwise to the disarm position, the key cannot be removed. To remove key, turn back to arm mode, thus keeping unit armed always.
  - 2. **Standard arming mode** when key is inserted turning counter clockwise will disarm and key can be removed. Turning key clockwise will arm and key can be
- Improve security at any door, and stop door-propping vulnerability
- Sweeping 95db alarm &/or strobe
- "Always Armed" when key is removed or Standard Arming modes
- Narrow Stile, advanced microprocessor control
- Easy installation
- Relay option
- Tamper supervised
- Entry Delay Options: 15 seconds; 1 min. 15 sec.; 3 mins 15 sec.
- Unauthorized use of door causes alarm to sound and activates LED indicator &/or optional strobe on MSS/MBS models (shown left)
- Choose continuous alarm, minute shutdown with auto reset and exit/entry
- Tamper switch supervised
- For exterior key control, optional RIM cylinder may be used
- Metallic silver or duronodic finish. Red Armed Status Indicator.
- Relay option. Option for continuous power with external power supply added.
- Uses standard mortise cylinder (not included)



#### **Model PG30KPD:**

#### Keypad-controlled narrow stile door alarm, similar to PG21, plus:

- Digital codes for master, management and passage (used for auto-arming)
- 3 security levels for: a) high security b) unattended applications c) flexible control for delivery doors, etc.
- Audible low battery warning
- 3 Programmable 95db siren styles: sweep, pulsed, and steady
- Logo key is dual function test button

### **PG30KPD Accessory:**

• For optional use with the PG30, this low-profile, brushed aluminum finished accessory provides all functions of the PG30 from the outside of the door. (Available in metallic silver only.)

#### **Model PG10**

• The Pilfergard Model PG10 is an exit door alarm designed to deter the use of the secured door by sounding a twin action alarm when opened by unauthorized personnel. The alarm can be bypassed from inside or outside by the use of a key. (Requires standard mortise cylinder not supplied.) This durable surface mount unit is easily installed and is tamper-supervised with two separate tamper switches. Its test button verifies battery. Optional AC power supply available.

#### Model LL1

- All of the features of the PG10 unit with addition of a flashing strobe for easy alarm identification.
- Choice of system controllers

