

SPECIFICATIONS

System	
Main Processor	Dual-core embedded processor
Operating System	Embedded LINUX
Video	
IP Camera Input	Up to 8 channel
Two-way Talk	1 channel input, 1 channel output, BNC
Display	
Interface	1 HDMI, 1 VGA
Resolution	1920 x 1080, 1280 x 1024, 1280 x 720, 1024 x 768
Display Split	1/4/8/9
OSD	Camera title, time, video loss, camera lock, motion detection, recording
Recording	
Compression	H.264/MJPEG
Resolution	5Mp, 3Mp, 1080p, 720p, D1
Record Rate	200Mbps
Bit Rate	48~ 8192kbps
Record Mode	Manual, Schedule (regular/continuous, MD, alarm), stop
Record Interval	1-120 minutes (default: 60 minutes), pre-record: 1-30 seconds, post-record: 10-300 seconds
Video Detection & Alarm	
Trigger Events	Recording, PTZ, tour, alarm, video push, email, FTP, buzzer, screen tips
Video Detection	Motion detection, camera blank
Alarm Input	4 channel
Relay Output	2 channel

Playback & Backup	
Sync Playback	1/4/9
Search Mode	Time/date, alarm, MD & exact search (accurate to second), smart search
Playback Function	Play, pause, stop, rewind, fast play, slow play, next file, previous file, next camera, previous camera, full screen, repeat, shuffle, backup selection, digital zoom
Backup Mode	USB device, network, internal SATA burner
Network	
Ethernet	1 RJ-45 port (10/100/1000Mbps)
PoE	8 ports (IEEE802.3af)
Network Function	HTTP, TCP/IP, IPv4/IPv6, UPNP, RTSP, UDP, SMTP, NTP, DHCP, DNS, IP Filter, PPPOE, DDNS, FTP, alarm server, IP Search
Maximum User Access	128 users
Smart Phone	iPhone, iPad, Android
Storage	
Internal HDD	2 SATA ports, up to 8TB
Auxiliary Interface	
USB	2 ports (1 rear USB3.0, 1 Front USB2.0)
RS232	1 port, for PC communication and keyboard
RS485	1 port, for PTZ control
General	
Power Supply	AC 100-240V, 50/60Hz
Power Consumption	NVR: 60W (without HDD); PoE: Maximum 15W (each)
Working Environment	-10°C - 55°C (14°F - 131°F)
Dimensions	375mm x 285mm x 50mm (14.76in x 11.22in x 1.97in)
Weight	2.3kg (5.07 pounds) without HDD

Model Number	Model Description
HOLNVR081008P	HOLIS, 8 CH NVR, 8 Port POE, 1TB
HOLNVR082008P	HOLIS, 8 CH NVR, 8 Port POE, 2TB
HOLNVR084008P	HOLIS, 8 CH NVR, 8 Port POE, 4TB
HOLNVR086008P	HOLIS, 8 CH NVR, 8 Port POE, 6TB
HOLNVR088008P	HOLIS, 8 CH NVR, 8 Port POE, 8TB

