100, 300, 400 Series Alarmed Hardware

Premier Product

100, 300, 400 Series trim

Exit Alarm Trim

Matching trim available to complement other series of cylindrical locks, BM Series Mortise locks, exit devices and alarms.

Finishes

Knobs: US3, US4, US10, US10B, US26, US26D

Levers: US26D, US10B

Plate: AL, BRZ



Sierra SRX
Knob: S Cast
Rose: R Wrought



Tudor TA
Knob: T Wrought
Rose: T Wrought

100, 300, 400 Series accessories

Functions

Passage – Trim always operative

Storeroom – Key retracts latch, key removable only when trim is locked

Classroom – Key locks/unlocks trim

Ordering Information:

Trim Type	Passage	Storeroom	Classroom
Lever	SRX01	SRX82	SRX87
Ball Knob	BD01	BD12	BD17
Tudor Knob	TA01	TA12	TA17
Plate	SF01	SF03	n/a



Ball BD
Knob: B Wrought
Rose: D Wrought



Thru Bolts

#S30 (300, 400 series, 1-3/4" doors).
#S32 (F-400 series, 1-3/4" doors).
Specify finish: AL, BRZ.
To add extra strength to mounting.

Narrow Stile Mounting Plates

#S73 (100 series).
#S74 (300 series).
#S75 (400 series).
Specify finish: AL, BRZ.
For doors with stile widths 1-3/4"–4".
Not for use with F-400 series.

Surface Magnet Pack

#580 Magnet and shim for 100 series (furnished with alarm).

Options:

Automatic Rearming

- Units are provided with spring loaded on/off switch. Switch automatically returns to the on position after removal of the key.
- Alarm can never be left off.
- Available for all alarm models.
- Prefix AR to catalog number.

Remote Monitor

- Alarm units are supplied with 8-foot leads of wire. Wire attached to the electronics assembly to allow monitoring from a remote location.
- Can be used in conjunction with Arrow S40 remote panel or with panel, light or bell provided by others.
- Closed loop circuitry provides highest security.
- Prefix RM to catalog number (not available on 110 or 130 models).

Continuous Alarm

- Horns will sound continuously after a violation has occurred—does not shut off after 2 minute alarm cycle.
- Only disarming by key operation will quiet the alarm.
- Remote power is recommended for units with this feature.
- Prefix CA to catalog number (not available on 110 or 130 models).

Remote Power

- Alarm units are supplied with 8-foot leads of wire. Wire attached to electronics assembly to power unit from an external source.
- Can be used in conjunction with Arrow S63 Hard Wired Battery Eliminator or by other remote 9V power source.
- Prefix RP to catalog number (not available on 110 and 130 models).

Strikes:

S38
300/400 Series standard for single door applications.
Black nylon coated.



S24
F-400 Series standard for single door applications.
Black nylon coated.



S36
300/400 Series for double door applications without a mullion.
Surface applied.
Black nylon coated.



ASSA ABLOY, the global leader in door opening solutions

ARROW LOCK & DOOR HARDWARE
ASSA ABLOY