

PRO-LOK[®]

The Blue Punch™ Key Machine is a dedicated punch machine designed to provide factory original keys. The Blue Punch™ Key Machine creates keys at the speed of a duplicator and is fast, extremely accurate, and easy to use. The Blue Punch™ Key Machine is set up at the factory to provide automatic spacing and depth. An ideal key machine for the system integrator, commercial locksmith, hotels, housing complexes, schools, and other institutions. Fast and easy to use, the Blue Punch™ is a precision machine to the tightest tolerances. Portable, dependable, and hand operated - no electrical outlet needed.

BLUE PUNCH KEY MACHINE™ KEYWAY SPECIFICS

ITEM #	DESCRIPTION	SPECIFIC KEYWAYS
BP201ARFC	ARROW FLEXCORE	• Arrow Flexcore 51, 52, 53, 54, 61, 81, 83, 84 *will cut A3 & A4 w/purchase of code bar
BP201C70	CORBIN C70	• Most Popular Corbin System 70 Keyways 59 Series A1, A2, B1, B2, 60 Series 6 pin
BP201DE	DEXTER / MASTER	• Master Door Locks, All Dexter Cylinder
BP201FW	FALCON / WEISER	• Falcon Standard (Non I/C) - *will Not Cut 8 Or 9 Depths, All Weiser Cylinders
BP201HA	HAGER	• Hager Key Sections H (I.E. H1, H2, H3, H12, H23, H123, etc)
BP201IC	I-CORE	• A2 Standard Interchangeable Core (I/C) - * will cut A3 & A4 w/purchase of code bar • Best, Falcon & Arrow Small Format I/C Key Sections A-R, TA-TE, W Arrow 1A-4D • Exclusions: Arrow Flexcore, Kaba Peaks, Insta-Key
BP201IC-A3	I-CORE A3 SYSTEM	• Interchangeable Core (I/C) A3 System * will cut A2 & A4 w/purchase of code bar
BP201IC-A4	I-CORE A4 SYSTEM	• Interchangeable Core (I/C) A4 System * will cut A2 & A3 w/purchase of code bar
BP201KW	KWIKSET	• Kwikset Standard - *Titan - *Will Not Cut Square 1st Cut, Yale residential
BP201MB	MARSHALL BEST	• Marshall Best Keyways. Call PRO-LOK for keyway verification.
BP201ME07	MEDECO KM - 7°	• Medeco 7° Keyways
BP201ME14	MEDECO KM - 14°	• Medeco 14° Keyways
BP201SC	SCHLAGE - CLASSIC	• Schlage Classic (Including I/C) Obverse Key Sections Only C, CE, E, EF, F, FG, G, H, J, K, L (Aftermarket L Blanks Only) • Primus - Same Key Sections As Obverse Except A "P" Has Been Added To Keyway # (ie: CP, CEP, EP, ...Etc.) • Schlage Everest - C Key Sections (I.E. C123, C124, C126, C135, C145..... etc.) (Including I/C) • Everest Primus - Uses Same Names • Everest 29 S Key Sections (S + 3 Digits) • Exclusions: Numbered Key Sections, Quad Key Sections, Reverse Key Sections, Everest-B (B+3 Digits), Everest-D (D+3 Digits)
BP201SCB	SCHLAGE -SMALL FORMAT	• Schlage Everest - B Key Sections Only - B123, B125, B234, B235, All Other Keys With A B + 3 Digits • Everest 29 R Key Sections (R + 3 Digits) * will cut A3 & A4 w/purchase of code bars
BP201SCD	SCHLAGE - EVEREST D	• Schlage Everest - D Key Sections Only - D120, D123, D124, D134, D135, D145, D234, D235, D245, D345, All Other Keys With a D + 3 Digits • Everest 29 T Key Sections (T + 3 Digits)
BP201SCRV	SCHLAGE - REVERSE	• Schlage Reverse Sections - D,DQ,QQS,S,T,U,V,W &Y
BP201WK	WESLOCK	• All Weslock Cylinders
BP201YA	YALE	• Yale KeyMark Key Sections Only - 2A, 2C, 2D, 2E, 2F



BLUE PUNCH KEY MACHINE™ PARTS AND ACCESSORIES



BP-CASE
Blue Punch Case



Take your Blue Punch™ almost anywhere with this specialty constructed Blue Punch™ case. The case is designed from rugged hard plastic and includes a sturdy handle to make transportation easier. The inside has a customized area to support your Blue Punch™ machine and a special area for your code bar.