

# Parts and accessories - replacement shackles



Part #	Shackle Dimension			Shackle Dimension (metric)			Box Qty	Carton Qty
	A	B	C	A	B	C		
<b>Hardened steel shackles - for use with 10 series padlocks</b>								
KZ11A10	1/4"	3/4"	3/4"	6.4 mm	19 mm	19 mm	6	36
KZ11D10	1/4"	1 1/2"	3/4"	6.4 mm	38 mm	19 mm	6	36
KZ11F10	1/4"	2"	3/4"	6.4 mm	51 mm	19 mm	6	36
KZ11G10	1/4"	4"	3/4"	6.4 mm	102 mm	19 mm	6	36
<b>Hardened steel shackles - for use with 20 Series padlocks</b>								
KZ11A20	5/16"	3/4"	3/4"	8 mm	19 mm	19 mm	6	36
KZ11D20	5/16"	1 1/2"	3/4"	8 mm	38 mm	19 mm	6	36
KZ11F20	5/16"	2"	3/4"	8 mm	51 mm	19 mm	6	36
KZ11G20	5/16"	4"	3/4"	8 mm	102 mm	19 mm	6	36
<b>Hardened steel shackles - for use with 40 Series padlocks</b>								
KZ11A40	3/8"	3/4"	3/4"	9.5 mm	19 mm	19 mm	6	36
KZ11D40	3/8"	1 1/2"	3/4"	9.5 mm	38 mm	19 mm	6	36
KZ11F40	3/8"	2"	3/4"	9.5 mm	51 mm	19 mm	6	36
KZ11G40	3/8"	4"	3/4"	9.5 mm	102 mm	19 mm	6	36
<b>Brass shackles - for use with 10 Series padlocks</b>								
KZ12A10	1/4"	3/4"	3/4"	6.4 mm	19 mm	19 mm	6	36
KZ12D10	1/4"	1 1/2"	3/4"	6.4 mm	38 mm	19 mm	6	36
KZ12F10	1/4"	2"	3/4"	6.4 mm	51 mm	19 mm	6	36
KZ12G10	1/4"	4"	3/4"	6.4 mm	102 mm	19 mm	6	36
<b>Brass shackles - for use with 20 Series padlocks</b>								
KZ12A20	5/16"	3/4"	3/4"	8 mm	19 mm	19 mm	6	36
KZ12D20	5/16"	1 1/2"	3/4"	8 mm	38 mm	19 mm <td 6	36	
KZ12F20	5/16"	2"	3/4"	8 mm	51 mm	19 mm	6	36
KZ12G20	5/16"	4"	3/4"	8 mm	102 mm	19 mm	6	36
<b>Brass shackles - for use with 40 Series padlocks</b>								
KZ12A40	3/8"	3/4"	3/4"	9.5 mm	19 mm	19 mm	6	18
KZ12D40	3/8"	1 1/2"	3/4"	9.5 mm	38 mm	19 mm	6	18
KZ12F40	3/8"	2"	3/4"	9.5 mm	51 mm	19 mm	6	18
KZ12G40	3/8"	4"	3/4"	9.5 mm	102 mm	19 mm	6	18
<b>Accessories</b>								
KZ200AL	9" Retaining nickel plated steel chain						6	36

Shackle dimensions

