


DK-37

Digital Keypad

Digital Keypad for Narrow Stile Applications

The DK-37 digital keypad offers Wiegand output for universal compatibility with access control systems. The fully weatherproof stainless steel keypad is designed for narrow stile applications.



PRODUCT FEATURES

- 12-key cast stainless steel 2x6 keypad with silicone rubber keys
- Weatherproof and vandal resistant
- Dual voltage 12VDC or 24VDC
- Mounts on narrow mullion
- Compatible with access control systems using standard Wiegand output
- Red, green and yellow status LEDs
- Audible keystroke echo
- 16 foot (4.88m) Wiegand cable included
- MagnaCare Lifetime Replacement No Fault Warranty

PRODUCT OPTIONS

- DKC Digital Controller

SPECIFICATIONS

- FCC Part 15 & Industry Canada Compliant
- Patents Pending

Dimensions:
1-1/2"W x 7"H x 1"D

Electrical:
35mA Active, 7mA at Rest at 12VDC
75mA Active, 16mA at Rest at 24VDC

Operating Temperature:
-22 to +158F [-30 to +70C]
Indoor or outdoor use

Endurance:
1,000,000 cycles

Shipping Weight:
1.75lbs [0.8kg]

Finishes:
US32D/630 - Satin Stainless Steel
BK - Black Powder Coat

» MODELS

PART # | Description

DK-37SS	Digital Keypad - Wiegand, Narrow Stile, Satin Stainless
DK-37BK	Digital Keypad - Wiegand, Narrow Stile, Black




DK-38

Digital Keypad

Digital Keypad for Indoor Applications

The DK-38 digital keypad offers Wiegand output for universal compatibility with access control systems or the Securitron DKC. The 3x4 illuminated keypad features a flush-mount stainless steel faceplate.



PRODUCT FEATURES

- 12-key illuminated 3x4 keypad
- Dual voltage 12VDC or 24VDC
- Compatible with access control systems using standard Wiegand output
- Single gang mounting
- Red, green and yellow status LEDs
- Tamper detection
- True 10-digit operation
- Audible keystroke echo
- 16 foot (4.88m) Wiegand cable included
- MagnaCare Lifetime Replacement No Fault Warranty

PRODUCT OPTIONS

- DKC Digital Controller
- Weather-resistant cover
- Weather resistant back box

SPECIFICATIONS

- FCC Part 15 & Industry Canada Compliant

Dimensions:
2-3/4"W x 4-1/2"H x 1-1/8"D

Electrical:
52mA Active, 24mA at Rest at 12VDC
110mA Active, 50mA at Rest at 24VDC

Operating Temperature:
+32 to +110F [0 to +43C]
Indoor use

Endurance:
1,000,000 cycles

Shipping Weight:
1.5lbs [0.68kg]

Finish:
US32D/630 - Satin Stainless Steel

» MODELS

PART # | Description

DK-38	Digital Keypad - Wiegand, Single Gang, Satin Stainless
-------	--



SECURITRON
ASSA ABLOY