

FULL MORTISE BALL BEARING HINGES

COMMERCIAL HINGES

Standard weight doors receiving average frequency service (standard weight hinges) and high frequency service (heavy weight hinges). Designed to have both leaves mortised into the door and the jamb. The hinge sits flush with the surface of the door and frame.



FULL MORTISE 4-BALL BEARING HINGES, HEAVY WEIGHT

ITEM	SIZES	GAUGE	TYPE	FINISHES	BOX QTY	CASE QTY
BB52454	4-1/2" x 4"	.180	Square Corner	USP, US26D, US10A, US4, US3, US26, US32D, US32DNRP	3	48
BB5200	4-1/2" x 4-1/2"	.180	Square Corner	USP, US26DNRP, US10A, US10B, US10, US10BNRP, US3, US3NRP, US4, US32DNRP	3	48
TABB5200	4-1/2" x 4-1/2"	.180	Square Corner	US26DNRP, US32DNRP	3	48
SB BB5200	4-1/2" x 4-1/2"	.180	Square Corner	US10A, US10B, US10BNRP, US26DNRP	3	48
BB5254	5" x 4"	.190	Square Corner	USP, US26D, US10A, US10B, US32D	3	48
BB5210	5" x 4-1/2"	.190	Square Corner	USP, US26D, US26DNRP, US10, US10A, US10B, US10BNRP, US3, US4, US26, US32D	3	48
BB5500	5" x 5"	.190	Square Corner	US26DNRP, US32D, US10B	3	48

FULL MORTISE 2-BALL BEARING HINGES, STANDARD WEIGHT

ITEM	SIZES	GAUGE	TYPE	FINISHES	BOX QTY	CASE QTY
BB SC77	3-1/2" x 3-1/2"	.123	Square Corner	USP, US26D, US10A, US10B, US4, US3, US5, US32D	2	100
BBRC-5835	3-1/2" x 3-1/2"	.123	Round Corner 3/8" radius	US26D		
BBSC-33	3-1/2" x 3-1/2"	.123	Square Corner	US32D	2	100
BB SC56	4" x 4"	.130	Square Corner	USP, US1D, US26D, US10, US10A, US15A, US10B, US15, US4, US3, US5, US26, US32D	3	48
BB RC45	4" x 4"	.130	Round Corner 1/4" radius	USP, US1D, US26D, US10, US10A, US10NRP, US15A, US10B, US15, US4, US3, US5, US26, US32D, DURO	3	48
BB RC5844	4" x 4"	.130	Round Corner 3/8" radius	US26D, US15A, US10B, US15, US4, US3, US26	3	48
BB454	4-1/2" x 4"	.134	Square Corner	USP, US26D, US26DNRP, US10A, US10B, US4, US3, US26, US1DNRP, US32DNRP	3	48
RCBB454	4-1/2" x 4"	.134	Square Corner	US1NRP, US26DNRP	3	48
BB31	4-1/2" x 4-1/2"	.134	Square Corner	USP, USPNRP, US26D, US26DNRP, US10A, US10ANRP, US10B, US10BNRP, US10, US10NRP, US15A, US15, US4, US4NRP, US3, US3NRP, US5, US26, DURO, US1D, US32D, US32DNRP	3	48
TABB31	4-1/2" x 4-1/2"	.134	Square Corner	US26D, US26DNRP, US32DNRP	3	48
SB BB31	4-1/2" x 4-1/2"	.134	Square Corner	US26D, US10A, US10ANRP, US10B, US3, US26, US4	3	48
BB14031	4-1/2" x 4-1/2"	.134	Square Corner	US26D, US10B, US4, US15, US26, USP	2-SH140 1-BB31	32-SH140 16-BB31
BB54	5" x 4"	.134	Square Corner	US26D, US10A, US3, US32D, USP	3	48
BB545	5" x 4-1/2"	.146	Square Corner	USP, US26, US26D, US10, US10A, US10B, US3, US4, US32D	3	48
TABB545	5" x 4-1/2"	.146	Square Corner	US26D, US32D	3	48
BB55	5" x 5"	.146	Square Corner	US26D, US4, US3, US26, US10B, US10, US32D	3	48

Other sizes and finishes available upon request. Refer to catalog for stock availability.
Hinges are available in Steel, Stainless Steel and Solid Brass base. Refer to catalog for stock material.



CAL ROYAL PRODUCTS, INC.
6605 Flotilla Street, City of Commerce, California 90040 U.S.A.
Phone: (323) 888-6601; (800) 876-9258 • Fax: (323) 888-6699; (800)222-3316
Email: sales@cal-royal.com • Website: www.cal-royal.com

