

touchbar

| Item | Part No. | Description |
|------------------|------------------|---|
| 1 | | Latch Case Assembly (Reversible) Specify Hand |
| | 60-7000-0419-048 | 7100 |
| | 60-7000-0425-048 | 7100F |
| | 60-7200-0354-048 | 7200, 7200M |
| | 60-7200-0362-048 | 7200MF |
| | 60-7150-0005-048 | 7150, 7150F |
| | 60-7250-0001-048 | 7250, 7250M(F) |
| | 60-7010-0360-048 | 7110(F), 7170(F) |
| | 60-7210-0354-048 | 7210, 7210M(F) |
| | 60-7020-0360-048 | 7120(F), 7160(F) |
| | 60-7220-0354-048 | 7220, 7220M(F) |
| | 60-7030-0382-048 | 7130(F) (Includes Trim Slide) |
| 2 | | *Cover, Latch Assembly |
| | 60-7100-X026-FIN | 7100 |
| | 60-7000-X111-FIN | 7200, 7200M |
| | 60-7150-X001-FIN | 7150 |
| | 60-7250-X001-FIN | 7250, 7250M |
| | 60-7110-X003-FIN | 7110, 7170 |
| | 60-7010-X069-FIN | 7210, 7210M |
| | 60-7100-X025-FIN | 7120, 7160, 7130 |
| 60-7000-X353-FIN | 7220, 7220M | |
| 3 | | Bottom Rail |
| | 60-7000-X079-FIN | 36" 7100 Series |
| | 60-7200-X058-FIN | 36" 7200 Series |
| 5 | | Bar & Carrier Assembly |
| | 60-7000-0423-000 | 36" 7100 Series |
| | 60-7200-0356-000 | 36" 7200 Series |
| 6 | | 48" 7100/7200 Series |
| | 60-7000-X083-FIN | 36" |
| | 60-7000-X084-FIN | 48" |
| 7 | | Cover, Bar |
| | | Cover, End |
| | 60-7000-X359-FIN | 36" std. 7100 Series |
| | 60-7000-X362-FIN | 36" 7100 Series Cylinder Dogging |
| | 60-7200-X360-FIN | 36" std. 7200 Series |
| | 60-7200-X363-FIN | 36" 7200 Series Cylinder Dogging |
| 8 | 60-7200-X361-FIN | All 48" std. |
| | 60-7200-X364-FIN | All 48" Cylinder Dogging |
| | 60-7000-6115-999 | Touch Pad Cap, Front |
| 9 | 60-7000-6120-999 | Touch Pad Cap, Rear |

| Item | Part No. | Description |
|------|------------------|--|
| 10 | 60-7000-9088-999 | Bar Cap, Black Nylon |
| 11 | 60-7000-X360-FIN | End Cap |
| 12 | 60-7200-9216-999 | Trim Slide (All except Mortise) |
| 13 | 60-7000-1320-048 | Trim Slide Retainer |
| 14 | | Dogging Assembly |
| | 60-7000-0406-048 | Standard Hex Key Dog. |
| | 60-7000-0407-048 | Cylinder, Dogging |
| 15 | 60-7000-1131-036 | Dogging Key (5/32" hex) |
| 16 | 99-9999-4123-999 | Dogging Hole Plug |
| 17 | 60-7000-2421-000 | Cylinder Nut |
| 18 | 60-2000-9153-999 | Cylinder Spacer Sleeve |
| 19 | | Collar, Dogging Cylinder |
| | | None Required |
| | 10-1765-X001-FIN | 1-1/8" Cylinder |
| | 10-1765-X013-FIN | 1-1/4" Cylinder |
| | 10-1765-X013-FIN | 1-1/2" Cylinder |
| 20 | As Ordered | Dogging Cylinder (Mortise) |
| 21 | 81-9500-0605-FIN | End Clamp Packet |
| | | Consists of the following: |
| | 60-7000-1423-048 | End Clamp (4 Wood Screws) |
| | 60-7000-1349-048 | Mounting Screws (4) |
| | 60-7000-1131-036 | Hex Dogging Key (Except Fire Rated) |
| | 81-9500-1549-FIN | Cover Screw Packet (6) |
| 22 | 60-7000-1391-999 | Screw, Touch Bar Caps, Torx Cap #6-32 x 3/4" (4) |
| 23 | 81-9500-1549-FIN | Screw Packet, Cover #8-32 x 5/16" FHUM-PH (5) |
| 24 | 81-4414-0514-048 | Screw, Dogging Assy., #10-24 x 5/8" PHT-T-PN (2) |
| 25 | 81-3711-0412-048 | Screw, Trim Slide, #8-32 x 1/2" FHT-PH |
| 26 | 81-4014-0404-048 | Screw, Latch Head to Carrier, #8-32 x 1/4" PHTC-PH (2) |
| 28 | 03-0080-5047-FIN | Sex Nut Packet (4) Fire-rated Devices incl. |
| 54 | 81-4214-0508-036 | Screw, #10-24 x 3/8 Type F THP (4) |
| 56 | 81-9500-0620-FIN | Flush End Cap Kit |

*Covers which bare the UL Listing mark for Fire-Rating cannot be shipped with that marking. Therefore, covers for Fire-Rated Latch Case Assemblies are not available.