



US-C3 4-Door Kit



Add **12V DC PoE SPL**
option to eliminate
need for hard-wired
power (supports
only 1 & 2 Door kits)



Add **InBridge Server**
option to eliminate
need for downloading
management
software



Add **Wireless Bridge**
option to eliminate
data cable between
door controller
and network

C3 IP-based RFID card Access Control Kit

- Easy to install and program
- Often uses very same wiring & power from existing systems
- FREE user-friendly browser-based ZKAccess management software
- Stores up to 30,000 cards and 100,000 events
- Connects with KR500E slave card reader(s) via Wiegand
- Optional 12V 2A PoE splitter (supports only 1 & 2 Door Kits) InBridge Server and Wireless Bridge

C3 Kit part numbers

US-C3-1 Door Kit	US-C3-2 Door Kit	US-C3-4 Door Kit	Parts included:
1	1	1	C3 panel, power supply and metal can (enclosure)
1	1	1	CR10E card enrollment reader
1	2	4	KR500E IP65-rated slave prox card reader(s)
1	2	4	PTE-1 Request to Exit button(s)
1	1	1	ZKAccess management software
50	50	50	50 Proximity cards (clamshell type)



US-InBio 4-Door Kit



Add **12V DC PoE SPL**
option to eliminate
need for hard-wired
power (supports
only 1 & 2 Door kits)



Add **InBridge Server**
option to eliminate
need for downloading
management
software



Add **Wireless Bridge**
option to eliminate
data cable between
door controller
and network

InBio IP-based Biometric Access Control Kit

- Panel can store and match fingerprint templates on-board
- Completely eliminates the need for fingerprint-template management
- Easy to install and program
- Often uses very same wiring & power from existing systems
- FREE user-friendly browser-based ZKAccess management software
- Stores up to 3,000 fingerprint templates, 30,000 cards and 100,000 events
- Connects with FR1200-ID slave fingerprint reader(s) via RS485
- Optional 12V 2A PoE splitter (supports only 1 & 2 Door Kits) InBridge Server and Wireless Bridge

Inbio Kit part numbers

US-inBio-1 Door Kit	US-inBio-2 Door Kit	US-inBio-4 Door Kit	Parts included:
1	1	1	InBio panel, power supply and metal can (enclosure)
1	1	1	ZK4500 fingerprint enrollment reader
1	2	4	FR1200-ID IP65-rated slave fingerprint + prox card reader(s)
1	2	4	PTE-1 Request to Exit button(s)
1	1	1	ZKAccess management software

TF1700 TF1600 F18-ID FV350-ID MB700-ID



Outdoor
Fingerprint
Prox card
PIN code



Outdoor
Fingerprint
Prox card



Indoor
Fingerprint
Prox card
PIN code



Indoor
Fingerprint/
Finger vein
Prox card
PIN code



Indoor
Fingerprint/
Face
Prox card
PIN code

IP-based Fingerprint, Facial, Finger Vein and RFID card Access Control Readers

- Easy to install & program. No need for panel nor computer.
- Often use very same wiring & power from existing readers
- FREE user-friendly ZKAccess management software
- Choice of Indoor (F18-ID, FV350-ID, MB700-ID) and Outdoor (TF1700, TF1600) models
- Communication ports include TCP/IP, Wiegand In/Out, USB and RS232/485
- Relay contacts for Lock, Alarm and Exit button (REX)
- FAST and highly accurate Fingerprint, Facial, Finger Vein, RFID and PIN code recognition
- Optional 12V 2A PoE splitter