

*** BILL OF MATERIAL ***

PT NO.	CATALOG NO.	QTY	DESCRIPTION
1	PATCASEL1	1	CASE, TOOL PATRIOT® LITHIUM-ION
2	BAT18VLI	2	BATTERY, LITHIUM ION 18V
3	LIMSDS	1	MSDS, LITHIUM ION BATTERY
4	PATCHGRL1	1	CHARGER, BATTERY LITHIUM ION
5	BATCHGRLIOMI	1	BATTERY CHARGER SAFETY OPERATING MAINTENANCE & INSTRUCTIONS
6	PT208620	1	LANYARD
7	PAT750LIOMI	1	SOMI, PAT750-LI
8	PT20443801	1	FIVE YEAR WARRANTY CARD

CATALOG NUMBER	DESCRIPTION	CHARGER CATALOG NO.
PAT750-LI	PATRIOT® 750 WITH 120V CHARGER	PATCHGRL1
PAT750-LIDC	PATRIOT® 750 WITH 12V DC CHARGER	PATCHGRLIDC
PAT750-LI250V	PATRIOT® 750 WITH 250V CHARGER	PATCHGRLI250V
PAT750C-LI	PATRIOT® 750 (COVERED HEAD) WITH 120V CHARGER	PATCHGRL1
PAT750C-LIDC	PATRIOT® 750 (COVERED HEAD) WITH 12V DC CHARGER	PATCHGRLIDC
PAT750C-LI250V	PATRIOT® 750 (COVERED HEAD) WITH 250V CHARGER	PATCHGRLI250V

PATRIOT®

BATTERY ACTUATED TOOL - HYDRAULIC SELF CONTAINED - 12 TON OUTPUT FORCE

SPECIFICATIONS

- CRIMP FORCE: 12 TONS (10.9 METRIC TONS)
- TOOL WEIGHT: 15.7 LBS (7.1 kg)
- LENGTH: 15.75 (40.00 cm)
- WIDTH: 3.50 (8.89 cm)
- HEIGHT: 13.50 (34.29 cm)
- OPERATING VOLTAGE: 18V-DC
- RECHARGE TIME: 30 MINUTES


FEATURES AND BENEFITS

- REFINED HYDRAULIC SYSTEM FOR SUPERIOR PERFORMANCE, SPEED AND RELIABILITY.
- FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS.
- OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; ALLOWS FOR ONE-HANDED OPERATION FOR ADVANCE, RETRACT AND HOLD.
- 18 VOLT LITHIUM-ION BATTERIES PROVIDE 2.5 TIMES MORE CHARGE / DISCHARGE CYCLES THAN TRADITIONAL Ni-Cd BATTERIES AND PROVIDE 430% MORE LIFETIME WORK.
- 30 MINUTE CHARGER CONTROLS CURRENT, VOLTAGE AND TEMPERATURE TO MAXIMIZE BATTERY LIFE. FORCED AIR COOLING FAN COOLS THE BATTERY BY FORCING COOL AIR THROUGH THE BATTERY'S BUILT-IN AIR VENTS.
- STATE OF THE ART CRIMPING HEAD DESIGN, 355° ROTATION LETS THE USER GET INTO TIGHT AREAS EASIER.
- ALLOWS USE OF STANDARD BURNDY® DIES ALREADY IN USE.
- ERGONOMICALLY BALANCED TOOL DESIGN EASES OPERATION AND HELPS LESSEN FATIGUE.
- DURABLE HIGH IMPACT FORMED CARRYING CASE PROVIDES SUPERIOR PROTECTION AND STORES ALL ACCESSORIES.
- 5 YEAR LIMITED WARRANTY ON THE TOOL, 1 YEAR WARRANTY ON THE BATTERIES AND CHARGER.
- LIFETIME WARRANTY ON THE INFINITY DRIVE.

NOTES:

1. LANYARD IS STORED IN COMPARTMENT UNDER THE LID.

REV.	DATE	DESCRIPTION	ECO	BY	C'H.K.
B	9/22/2010 8:40:00 AM	ADD COVERED HEAD ITEM AND CATALOG NUMBERS ADD CARTON LABEL ITEM #30006459	22125	TRF	MAC



TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>

PATRIOT® BATTERY 12 TON CRIMPING TOOL

ITEM NO: --

CAT. NO: SEE TABLE

DRAWN BY: T. FAUCHER 05/06/2010
CHECKER: R. POIRIER 07/29/2010
DSN APPVL: M. CHIASSON 08/05/2010
MFG APPVL: S. GONYAW 08/19/2010
QA APPVL: J. BRODEUR 08/06/2010
MKT APPVL: -- --



PROD FAM:	TOOLS, BATTERY	DRAWING NO	REV
PROJECT #:	14074	30001518	B
DOCUMENT TYPE:	Sales	SHEET 1 OF 1	
REL LEVEL:	Released	SCALE: 1:4	