

5/8" & 3/4" ROUND DOOR PULLS

NUMBER	CTC	DIAMETER	DIMENSIONS			ANSI A156.6	MATERIAL
			OVERALL	PROJECTION	CLEARANCE		
11	5 1/2"	5/8"	6 1/8"	2"	1 3/8"	J401	Aluminum, Brass, Bronze, Stainless Steel
14	5 1/2"	3/4"	6 1/4"	2 1/4"	1 1/2"	J401	
15	6"	3/4"	6 3/4"	2 1/4"	1 1/2"	J401	
16	8"	3/4"	8 3/4"	2 1/4"	1 1/2"	J401	
17	10"	3/4"	10 3/4"	2 1/4"	1 1/2"	J401	

SHELF PACK: I **Box Pack**

FASTENERS: 1/4-20 Thru bolt & finish washer

FEATURE: Made from solid bar stock

FINISHES: 605, 606, 609, 613, 628, 629, 630

OPTIONS:

- Back to back mounting for pulls 3/4" dia. only
- Back to back mounting not available on 5/8" dia. Pulls
- Concealed Mounting
- Specify door thickness if greater than 1 3/4"
- Use prefix "H" for 2 1/2" clearance
- See page 14b for other mounting options

1" ROUND DOOR PULLS

NUMBER	CTC	DIAMETER	DIMENSIONS			ANSI A156.6	MATERIAL
			OVERALL	PROJECTION	CLEARANCE		
19	8"	1"	9"	3"	2"	J401	Aluminum, Brass, Bronze, Stainless Steel
20	10"	1"	11"	3"	2"	J401	
21	12"	1"	13"	3"	2"	J401	
22	18"	1"	19"	3"	2"	J401	

SHELF PACK: I **Box Pack**

FASTENERS: 1/4-20 Thru bolt & finish washer

FEATURE: Made from solid bar stock

FINISHES: 605, 606, 613, 628, 629, 630

OPTIONS:

- Back to back mounting for pairs
- Concealed Mounting
- Specify door thickness if greater than 1 3/4"
- Use prefix "H" for 2 1/2" clearance
- See page 14b for other mounting options

FLAT BAR DOOR PULLS

NUMBER	CTC	DIAMETER	DIMENSIONS			ANSI A156.6	MATERIAL
			OVERALL	PROJECTION	CLEARANCE		
30	6"	3/8" x 1 1/4"	6 3/8"	2"	1 5/8"	J401	Aluminum, Brass, Bronze, Stainless Steel
31	8"	3/8" x 1 1/4"	8 3/8"	2"	1 5/8"	J401	
32	10"	3/8" x 1 1/4"	10 3/8"	2"	1 5/8"	J401	

SHELF PACK: I **Box Pack**

FASTENERS: 1/4-20 thru bolt & finish washer

FEATURE: Made from solid bar stock

FINISHES: 605, 613, 628, 630