




| ITEM No. | PART No. | DESCRIPTION                        | REQ |
|----------|----------|------------------------------------|-----|
| 1        | 08-4321  | Knob, cylinder ("B" shown)         | 1   |
| 2        | 13-2194  | Cylinder Assembly                  | 1   |
| 3        | 76-0027  | Knob Collar                        | 2   |
| 4        | 08-0365  | Nylon Ring, outside (black)        | 1   |
| 4        | 08-0102  | Nylon Ring, inside (white)         | 1   |
| 5        | 08-0100  | Shank, outside                     | 1   |
| 5        | 08-0105  | Shank, outside (87)                | 1   |
| 5        | 08-0516  | Cylinder Shank, outside (70, 71)   | 1   |
| 6        | 09-0019  | Knob Retainer                      | 2   |
| 7        | 06-0185  | Knob Retainer Spring               | 2   |
| 8        | 08-2831  | Locking Spindle Assy.              | 1   |
| 8        | 08-2780  | Cam/Driver Assy. (87 Function)     | 1   |
| 8        | 08-4697  | Key Driver Assy., outside (70, 71) | 1   |
| 9        | 08-0214  | Spiral Cam Spring (37)             | 1   |
| 9        | 08-0407  | Cylinder Barrel Spring (70, 71)    | 1   |
| 10       | 76-0563  | Knob Pin                           | 2   |
| 11       | 08-2670  | Aligning Tube Assy. (37, 87)       | 1   |
| 12       | 08-0101  | Shank, inside                      | 1   |
| 13       | 08-0138  | Solid Driver, inside (37, 87)      | 1   |
| 13       | 08-0515  | Solid Driver, inside (70, 71)      | 1   |
| 14       | 08-0166  | Retainer Ring                      | 3   |
| 15       | 08-4320  | Knob, plain ("B" shown)            | 1   |
| 16       | 08-3312  | Rose ("O" shown)                   | 2   |

| ITEM No. | PART No. | DESCRIPTION                                              | REQ |
|----------|----------|----------------------------------------------------------|-----|
| 17       | 08-2510  | Guarded Latch Assy. (37)                                 | 1   |
| 17       | 08-2540  | Guarded Latch Assy. (87 Function)                        | 1   |
| 17       | 08-2517  | Latch Bolt Assy.— $\frac{1}{4}$ " throw (37) (41 prefix) | 1   |
| 17       | 08-4838  | Guarded Latch Assy. (70, 71)                             | 1   |
| 18       | 06-0176  | Aligning Pin (37, 87)                                    | 1   |
| 18       | 08-0675  | Aligning Pin (70, 71)                                    | 1   |
| 19       | 08-0200  | Hold Back Cam Pin (87)                                   | 1   |
| 43       | 01-5000  | # 8-32 x $\frac{1}{4}$ " Machine Screw                   | 2   |
| 60       | 08-4733  | Scalp and Aligning Tube Assy. (70, 71)                   | 1   |
| 61       | 08-4687  | Solenoid Assy. (71)                                      | 1   |
| 61       | 08-4688  | Solenoid Assy. (70)                                      | 1   |
| 62       | 08-0508  | Solenoid Cap (70, 71)                                    | 1   |
| 63       | 08-0509  | Solenoid Holder (70, 71)                                 | 1   |
| 64       | 01-1178  | Clamp Screw # 8-32 x $\frac{1}{4}$ " (70, 71)            | 1   |
| 65       | 01-0645  | Cable Clamp (70, 71)                                     | 1   |

## Parts List

Page No. Rev.  
8.8 B