



ACCESS reliability.

Application

The RF-programmable ProxKey® III proximity key fob incorporates proximity technology into a convenient device approximately the size of an automotive key.

Features

- ▶ Improved key fob design provides additional durability and more opportunity for customization.
- ▶ Offers universal compatibility with all HID proximity readers.
- ▶ Provides an external number for easy identification and control.
- ▶ Can be placed on a key ring for convenient entry.
- ▶ Supports formats up to 85 bits, with over 137 billion codes.
- ▶ Using HID's ProxProgrammer™, card vendors can ship proximity key fobs, custom programmed to their customers' requirements, from their own inventory. Enables smaller order quantities and overnight delivery. (Check with vendor for availability.)

Features

Proven, Reliable Technology

Offers extremely consistent read range. Unaffected by body shielding or variable environmental conditions, even when close to keys and coins.

Small and Convenient

Can be carried with keys in pocket or handbag.

Cross-reference


A cross-reference list correlating the external card number and the programmed ID number is provided for easy system administration.

Security

Offers over 137 billion unique codes.

Long Life

Passive, no-battery design allows for an infinite number of reads.



Base Part Number

1346

Description

RF-programmable, 125 kHz, black with grey insert, customer-specified ID Numbers

*Typical Maximum Read Range

ProxPoint® Plus reader up to 1.5" (3.7 cm)
MiniProx™ reader up to 2" (5 cm)
ThinLine® II reader up to 2" (5 cm)
ProxPro® reader up to 3" (7.5 cm)
ProxPro® II reader up to 4" (10.2 cm)
Prox80™ up to 2" (5.1 cm)
MaxiProx® reader up to 12" (28 cm)

Dimensions

1.555 x 1.25 x 0.235 inches max (3.95 x 3.18 x 0.60 cm)

Key Fob Construction

Ultrasonically welded ABS Shell with TPE insert

Operating Temperature

-50° to 160° F (-45° to 70° C)

Weight

0.14 oz (4.0g)

Memory Size/ Application Areas

N/A

HID Proximity 125 kHz

Yes

Contact Smart Chip Module Embeddable

No

Wiegand Stripe

No

Magnetic Stripe

No

Printable

No

Standard HID Artwork

Yes

Slot Punch

Key Ring Hole

Visual Security Options

N/A

Additional Security Options

Corporate 1000

Warranty

Lifetime

Options

Key Ring sold separately (Part Number: 57-0001-02)
External card numbering (inkjet or laser engraving)

*Dependent on local installation conditions.

© 2010 HID Global. All rights reserved. HID, and the HID logo are trademarks or registered trademarks of HID Global in the U.S. and/or other countries. All other trademarks, service marks, and product or service names are trademarks or registered trademarks of their respective owners. Rev. 4/2010



For best results, please print on recycled paper.

MKT-PROXKEYii_DS_EN



ACCESS experience.

HID Global Offices:

Corporate North America
15370 Barranca Parkway
Irvine, CA 92618-2215
U.S.A.
Phone: (800) 237 - 7769
Phone: (949) 732 - 2000
Fax: (949) 732 - 2360

Asia Pacific
19/F 625 King's Road
North Point
Island East
Hong Kong
Phone: +852 3160-9800
Fax: +852 3160-4809

Latin America
Vasco de Quiroga No. 1900 - 202
Centro Ciudad Santa Fé
Delegación Alvaro Obregón
01210 México, D.F.
Phone: +52 55 5081 1650
Fax: +52 55 5081 1670

Europe, Middle East & Africa
Homefield Road
Haverhill, Suffolk
CB9 8QP
England
Phone: +44 (0) 1440 714 850
Fax: +44 (0) 1440 714 840