

HANSON® 41-piece Machine Screw/Fractional Tap & Hex Die Set



24606

- Plastic storage case with removable tray keeps all tools organized

HANSON 41-piece Metric Tap & Hex Die Set



26317

Set Contents		Item # 24606
Thread Size	Tap Item #	Die Item #
Machine Screw	Plug Style	5/8" Hexagon
4 - 40 NC	1112ZR	6112
6 - 32 NC	1118	6118
8 - 32 NC	1124	6124
10 - 24 NC	1128ZR	6128
10 - 32 NF	1131	6131
12 - 24 NC	1132	6132
Fractional		1" Hexagon
1/4" - 20 NC	1420	6520ZR
1/4" - 28 NF	1423ZR	6523ZR
5/16" - 18 NC	1427	6527
5/16" - 24 NF	1429ZR	6529
3/8" - 16 NC	1434ZR	6534ZR
3/8" - 24 NF	1436	6536
7/16" - 14 NC	1439ZR	6539
7/16" - 20 NF	1440	6540
1/2" - 13 NC	1444ZR	6544
1/2" - 20 NF	1445	6545
Pipe		1" Hexagon
1/8" - 27 NPT	1902	6702
Threading Tools		Item #
Plain Die Stock - 5/8" Hexagon Dies		12457
Adj. Die Stock - 1" Dies		11026
Adj. Handle Tap Wrench - Taps No. 0 to 1/2"		311088
T-Handle Wrench - Taps No. 0 to 1/4"		12473
Two-in-One Tap Wrench - Taps 1/4" to 1/2"		12450
18 Leaf Standard Thread Pitch Gauge		11018
Empty Plastic Case		24606MT

Set Contents		Item # 26317
Thread Size	Tap Item #	5/8" Die Item #
Metric	Plug Style	Item #
3 mm - 0.50	1712ZR	6312
4 mm - 0.70	1717ZR	6317
4 mm - 0.75	1718ZR	6318
5 mm - 0.80	1722ZR	6322
5 mm - 0.90	1723ZR	6323ZR
6 mm - 1.00	1727	6327
		1" Die Item #
7 mm - 1.00	1731ZR	6631
8 mm - 1.00	1733ZR	6633
8 mm - 1.25	1734ZR	6634
9 mm - 1.00	1736	6636
9 mm - 1.25	1737	6637
10 mm - 1.25	1739	6639
10 mm - 1.50	1740ZR	6640
11 mm - 1.50	1741ZR	6641
12 mm - 1.50	1743ZR	6643
12 mm - 1.75	1744ZR	6644
Pipe		Item #
1/8" - 28 BSP	1911ZR	6711
Threading Tools		Item #
Plain Die Stock - 5/8" Hexagon Dies		12457
Adj. Die Stock - 1" Dies		11026
Adj. Handle Tap Wrench - Taps No. 0 to 1/2"		311088
T-Handle Wrench - Taps No. 0 to 1/4"		12473
Two-in-One Tap Wrench - Taps 1/4" to 1/2"		12450
18 Leaf Standard Thread Pitch Gauge		11018
Empty Plastic Case		24606MT