

SPEEDBOR® Spade Bit Sets



88885



1764344

SPEEDBOR Spade Bit Pro Set



341008

- Sliding latch design provides added security.



4935704



88702

Standard Spurless Spade Bits



88012BULK

Diameter	Length	Shank Size	Bulk Item
3/8"	6"	1/4" Hex	88006BULK
1/2"	6"	1/4" Hex	88008BULK
5/8"	6"	1/4" Hex	88010BULK
3/4"	6"	1/4" Hex	88012BULK
7/8"	6"	1/4" Hex	88014BULK
1"	6"	1/4" Hex	88016BULK
1-1/8"	6"	1/4" Hex	88018BULK
1-1/4"	6"	1/4" Hex	88020BULK
1-1/2"	6"	1/4" Hex	88024BULK

European Hinge Bits



IW14334

Diameter	Length	Shank Size	Bulk Item
26 mm	4"	1/4" Round	IW14334
35 mm	4"	1/4" Round	IW14335

Description	Diameter	Item #
Short Length Spade Bit Sets		
3-pc set	1/2", 3/4", 1"	87950
		87954
6-pc Pro Set w/Extension	3/4", 7/8", 15/16", 1", 1-1/8" Short Length Bits; 6" OAL Quick-Change Extension	1768411
Standard Length Spade Bit Sets		
3-pc Set	1/2", 3/4", 1"	88889
4-pc Set w/Extension	1/2", 3/4", 1", & 6" Quick-Change Extension	4935687
5-pc Set	3/8", 1/2", 5/8", 3/4", 1"	88885
6-pc Set	3/8", 1/2", 5/8", 3/4", 7/8", 1"	88886
6-pc Set w/Workshop Rack	3/8", 1/2", 5/8", 3/4", 7/8", 1" & Rack	88888
6-pc Set w/Extension	3/8", 1/2", 5/8", 3/4", 1" & 6" Quick-Change Extension	88898
8-pc Pro Set Case	3/8", 1/2", 5/8", 7/8", 1", 1-1/8", 1-1/2" & Pro Set Case	341008
10-pc SPEEDBOR Pro Set	3/8" x 6", 1/2" x 6", 5/8" x 6", 3/4" x 6", 7/8" x 6", 1" x 6", 1-1/8" x 6", 1-1/4" x 6", 1-3/8" x 6", 1-1/2" x 6"	1890204
13-pc Set	1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"	88894
13-pc Set w/Workshop Rack	1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1"	88887
17-pc Set	1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1", 1-1/8", 1-1/4", 1-3/8", 1-1/2"	1792761
17-pc Set	3/16", 1/4", 5/16", 3/8", 5/32" X 6", 3/16" X 6", 1/4" X 6", 3/8" X 6", 1/16, 5/64, 3/32, 7/64, 1/8, 9/64, 5/32, 3/16, 1/4	1890221
33-pc Set	3/8" x 6", 1/2" x 6", 5/8" x 6", 3/4" x 6", 7/8" x 6", 1/16, 5/64, 3/32, 1/8, 5/32, 3/16, 1/4, #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, #3 Square, T15, T20, T25, #2 Phillips, #2 Square, T20, T25, 15/16", 15/16", 1/4"	1890206
33-pc Set	3/8" x 6", 1/2" x 6", 5/8" x 6", 3/4" x 6", 7/8" x 6", #1 Phillips, #2 Phillips, #3 Phillips, #1 Square, #2 Square, #3 Square, 6-8, 8-10, 10-12, T10, T15, T20, T25, T27, T30, #2 Phillips, #2 Square, T20, T25, 2- 31/32", 3-1/16"	1890207
Slim Case Spade Bit Sets		
5-pc Set	3/8", 1/2", 5/8", 3/4", 1", Slim Case	1891777
7-pc Set	3/8", 1/2", 5/8", 3/4", 7/8", 1", 6" Quick Change-Extension	1891773
8-pc Set	3/8", 1/2", 5/8", 3/4", 7/8", 1", 1-1/8", 1-1/2"	1891776
10-pc Set	1/4", 3/8", 1/2", 5/8", 3/4", 7/8", 1", 1-1/4", 1-3/8", 1-1/2", Slim Case	1891774
12-pc Set	3/8", 3/8", 1/2", 1/2", 5/8", 5/8", 3/4", 3/4", 7/8", 7/8", 1", 1", Slim Case	1891775
Standard Length Spade Bit Bulk Packs		
4-pc Bulk Pack	5/8"	1764343
4-pc Bulk Pack	3/4"	1764344
4-pc Bulk Pack	1"	1764345
Lock-n-Load® Quick-Change Extensions		
1/4" Quick-Change Bit Holder 2-1/2" OAL / 5/8" OAW		4935703
1/4" Quick-Change Bit Holder 6" OAL / 5/8" OAW		4935704
1/4" Quick-Change Bit Holder 12" OAL / 5/8" OAW		4935705
Manual Locking Hex Key Extensions		
1/4" Hex Key Extension 6" OAL / 1-1/16" OAW		88702
1/4" Hex Key Extension 12" OAL / 1-1/16" OAW		88601


Hex Key Extensions compatible with:



IRWIN® Lock-n-Load® Quick-Change Extensions

QUICK-CHANGE BIT EXTENSION FEATURES

1. Lock-n-Load® system for quick release and fast bit changes.
2. Chrome-plated sleeve and body for improved durability and longer life.
3. Unique jaw design is compatible with 6-flatted shanks, ball detent (quick-change), and insert bits.
4. 1/4" range works with insert bits and is magnetic for additional holding power.



4935652

Lock-n-Load Compatibility

WOOD DRILLING

1/4"



- SPEEDBOR® Blue Groove (All Sizes)
- SPEEDBOR Max Speed (Sizes 7/16" to 1-1/4")
- Fastener Drive (All products)
- UNIBIT® (Sizes #1, #2, #10, #12)
- 1/4" Hole Saw Arbor (Sizes 9/16" to 1-3/16")
- Countersinks (Sizes #4 to #12)



3/8"



- SPEEDBOR Max Speed (Sizes 1-3/8", 1-1/4")
- UNIBIT (Sizes #3, #4, #11)
- 3/8" Hole Saw Arbor (Sizes 9/16" to 6" diameter saws)



7/16"



- 17" Ship Augers (Sizes 9/16" and larger)
- 7-1/2" Short Ship Augers (Sizes 1-1/8", 1-1/4")
- Self-Feed Bits (All sizes)
- UNIBIT (Sizes #5, #9, #13, #14, #20, #21)
- 1/2" Hole Saw Arbor (Sizes 1-1/4" - 6")



4935704

Description	Item #
1/4" Quick-Change Bit Holder 2-1/2" OAL / 5/8" OAW	4935703
1/4" Quick-Change Bit Holder 6" OAL / 5/8" OAW	4935704
1/4" Quick-Change Bit Holder 12" OAL / 5/8" OAW	4935705
3/8" Quick-Change Bit Holder 2-3/4" OAL / 7/8" OAW	4935651
3/8" Quick-Change Bit Holder 5-1/2" OAL / 7/8" OAW	4935652
3/8" Quick-Change Bit Holder 12" OAL / 7/8" OAW	4935653
7/16" Quick-Change Bit Holder 5-1/2" OAL / 1-1/16" OAW	4935654
7/16" Quick-Change Bit Holder 12" OAL / 1-1/16" OAW	4935655
7/16" Quick-Change Bit Holder 18" OAL / 1-1/16" OAW	4935656
1/4" Quick-Change Bit Holder 18" OAL	1869515



88702

Manual Locking Hex Extensions

Description	Item #
1/4" Hex Key Extension 6" OAL / 1-1/16" OAW	88702
1/4" Hex Key Extension 12" OAL / 1-1/16" OAW	88601
7/16" Hex Key Extension 6" OAL / 1-1/16" OAW	3046001
7/16" Hex Key Extension 12" OAL / 1-1/16" OAW	3046002
7/16" Hex Key Extension 18" OAL / 1-1/16" OAW	3046003

Hex Key Extension
Compatible With:

