

1200 Series

Heavy Duty Stops & Holders



1201 SHOWN

Trimco's **1200 Series** heavy duty door stops are offered in a wide range of models to suit many different needs. 1200 Series options include floor and wall mounting, holders, anti-vandal and extra heavy duty versions.

APPLICATIONS

- Offices
- K-12 Schools & Universities
- Retail & Strip Malls
- Commercial & Industrial Buildings

STOPS & HOLDERS

PRODUCT FEATURES

- Floor or wall mounted with options for holders
- CK versions are heavy duty, high-abuse, school design which reduces tampering and loss of rubber bumper
- Available with fasteners for surface mounted and anchored applications

SPECIFICATIONS

STANDARDS

BHMA L02121

FASTNERS

Wood screws for surface mounting" to "Combo Pack

MATERIAL OPTIONS

BR – Brass
BZ – Bronze
PL – Chrome Plated Brass
or Bronze Castings

WARRANTY

Lifetime Mechanical &
Limited Finish Warranty

FINISHES

605	Polished Brass
606	Satin Brass
609	Antique Brass
612	Satin Bronze
613	Oil Rubbed Bronze
619	Satin Nickel
620	Antique Nickel
622	Satin Black
625	Polished Chrome
625	Polished Chrome
SPEC	Special Options Available

1200 Series

Heavy Duty Stops & Holders

HOW TO SPECIFY & ORDER


CHOOSE THE FOLLOWING

SERIES		FINISHES	
1200	Cast Floor Stop 3", Wood Screws	605	Polished Brass
1200-5	Cast Floor Stop 5", Wood Screws	606	Satin Brass
1200CK	Cast Floor Stop 3", Torx Screws	609	Antique Brass
1201	Cast Floor Stop 3", Combo Pack	612	Satin Bronze
1201-5	Cast Floor Stop 5", Combo Pack	613	Oil Rubbed Bronze
1201CK	Cast Floor Stop 3", Torx Screws	619	Satin Nickel
1204	Base Stop, Wood Screws	620	Antique Nickel
1205	Base Stop, Combo Pack	622	Satin Black
1206	Base Stop & Holder, Wood Screws	625	Polished Chrome
1207	Base Stop & Holder, Combo Pack	626	Satin Chrome
1223	Floor Stop & Holder 3", Wood Screws	SPEC	Special Options Available
1224	Floor Stop & Holder 3", Combo Pack		
1224-5	Floor Stop & Holder 5", Combo Pack		


EXAMPLE

For a cast 3" floor stop with Torx screws in Satin Chrome finish, specify or order: **1201CK.626**


1201




1204



1207



1224



* Dimensions are informational only. Templates are available at www.trimcobbw.com