



# Jimmy-Proof Deadlock 197




## OPERATION

**Outside:** Furnished standard with 5-pin rim cylinder 1109E.  
**Inside:** 90° turn of the thumbturn locks or unlocks deadbolt. Also available with flat strike, model no. 197F (for outswinging doors).

Model Numbers	
197	Boxed
V197	Visual Pack
197F	Flat Strike, Boxed

## DIMENSIONS AND DETAILS



## TECHNICAL INFORMATION

Description	197
Backset	2-3/8" (60mm)
Material	Zinc Alloy
Deadbolt Length	N/A
Reversible Latchbolt	N/A
Cylinder	1109E - Brass 5-pin with anti-pick mushroom drivers
Case Finishes	Sprayed Brass only
Cylinder Finish	Brass
2 Keys	RB8
Door Thickness	1-1/4" to 2-1/4" (32mm-57mm)

Dimensions are shown in inches (millimeters).



# Jimmy-Proof Deadlock 197-1/4



## OPERATION


**Outside:** Furnished standard with 5-pin rim cylinder 1109E.

**Inside:** Key locks or unlocks deadbolt. Also available with flat strike, model no. 197-1/4F (for outswinging doors).

### Model Numbers

197-1/4	Boxed
V197-1/4	Visual Pack
197-1/4F	Flat Strike, Boxed

## DIMENSIONS AND DETAILS



## TECHNICAL INFORMATION

Description	197-1/4
Backset	2-3/8" (60mm)
Material	Zinc Alloy
Deadbolt Length	N/A
Reversible Latchbolt	N/A
Cylinder (Outside)	1109E Brass 5-pin with anti-pick mushroom drivers
Cylinder (Inside)	Fixed 3-pin Brass cylinder. No alternatives.
Case Finishes	Sprayed Bronze only
Cylinder Finish	Brass
2 Keys	RB8
Door Thickness	1-1/4" to 2-1/4" (32mm-57mm)

Dimensions are shown in inches (millimeters).




## Auxiliary Rim Lock Components

### CYLINDERS


Yale® auxiliary rim locks 80, 88, 112, 112-1/4, 197, and 197-1/4 are shipped standard with an 1109E brass, 5-pin, E1R (PARA) section rim cylinder. The 1109E is not available as a replacement cylinder.

**Note: 1109E depths and spacings are not compatible with other cylinders available from Yale Locks & Hardware.**

For alternative rim cylinders, refer to Yale® KeyMark® and/or Yale Cylinder and Keys catalog sections.




### STRIKES




**No. 197F Flat Strike**

Used with 197F and 197-1/4F for outswing doors.



**No. 112F Flat Strike**

Used with 112F and 112-1/4F for outswing doors.



**No. 8RB Rim Strike**

Used with 80 and 88 for outswing doors.

Dimensions are shown in inches (millimeters).