George Risk Industries

(800) 523-1227

Home Products About GRI Contact GRI Where to Buy Testimonials What's New!


505 Series Super Miniature Surface Mount Switch Sets



505 Super Miniature Surface Mount Switch Set

- Lifetime Warranty
- UL and ULC Approved
- Available in Open Loop or Closed Loop
- Standard 12" Leads
- Standard Gap 1/2"+
- Wide Gap 3/4"+
- Switches or Magnets are Available Separately

The 505 Super Miniature switch is aimed at residential applications where aesthetics and small size play a large consideration in the switch choice. It offers the installer two methods of mounting, alternative cable types (flying lead or zip cord), and a choice of cable lengths. All help to make installations and connections quick and easy, saving you time and money. Available in regular gap of 1/2"+ and a 1" wide gap version. The flexibility of its small overall size allow it to become part of the existing decor or it can be mounted and hidden, for example, in the track of a sliding door or crank out window. Offered in a White or Brown, with mounting brads and die cut double sided tape included with the switch sets.



SUPER MINIATURE SURFACE MOUNT SWITCH SET



505 SERIES

- ♦ When a Surface Mount is a Must 505 Is The Answer
- ◆ Ideal For Residential Applications and Areas With Limited Space
 - ◆ Surface Mount Magnetic Contact
 - ◆ 12" #22AWG Leads
 - ◆ Longer Leads, or Zip Cord Upon Request
 - ◆ Hermetically Sealed
 - ◆ Plated Contacts Resist Sticking or Freezing
 - ◆ Mounting Brads and Die Cut Double Sided Tape Included
 - ◆ Switches and Magnets Available Separately
 - ◆ Colors: White, Brown
 - ◆ Lifetime Warranty



PART NUMBERS:

Standard Gap 1/2"+

Wide Gap 3/4" +

Closed Loop



505WG

Open Loop








SUPER MINIATURE SURFACE MOUNT SWITCH SET

INSTALLATION APPLICATIONS:

The 505 super miniature switch is aimed at residential applications where aesthetics and small size play a large consideration in the switch choice. It offers the installer two methods of mounting, alternative cable types (flying leads or zip cord) and a choice of cable lengths. All help to make installations and connections quick and easy, saving you time and money. Available in regular gap of 1/2" + and a 3/4" + wide gap version. The flexibility of its small overall size allow it to become part of the existing decor. It can be mounted and hidden, for example, in the track of a sliding door or crank out window. The brad holes in both switch and magnet should be opposing to achieve correct installation. Offered in a white or brown, with mounting brads and die cut double sided tape included with switch sets. Also available as switch only or magnet only.



505

GRI products meet or exceed these minimum general specifications:

-							
PART NUMBE		ELECTRICAL CONFIG.	REED FORM	MAXIMUM INITIAL CONTACT RESISTANCE	MAXIMUM CONTACT RATING	MAXIMUM SWITCHING VOLTAGE	MAXIMUM SWITCHING CURRENT
				(Ω)	(W)	(VDC)	(A)
505	CLOSED	N/O	Α	.150	10	200	.500
505W0	G CLOSED	N/O	Α	.150	10	200	.500
506	OPEN	N/C	В	.140	5	175VDC	.250
506W0	G OPEN	N/C	В	.140	5	175VDC	.250

WARRANTY:

Lifetime warranty against workmanship, material and factory defects.

CONTACT YOUR G.R.I. DISTRIBUTOR OR CALL:

GEORGE RISK INDUSTRIES, INC. GR.I. PLAZA KIMBALL, NE 69145



TOLL-FREE 1-800-445-5218 TOLL-FREE 1-800-523-1227 (308) 235-4645 FAX (308) 235-3561

E-MAIL: grisales@megavision.com WEB SITE: www.grisk.com